

MICRO-CRIMP RECTANGULAR CONNECTORS

Series 792 High-Speed

SERIES
792
High-Speed

792-023

PCB Receptacle, 90° Tails, Quadrax

- ◆ Quadraxial PC tail contacts
- ◆ 90° mounting
- ◆ Pin contacts



792-023 receptacle has high-speed quadraxial PC tail socket contacts for 90° thru-hole printed circuit board termination. Contacts are potted with epoxy. Machined aluminum shell has integral standoff and threaded holes for attachment to PC board. Combo arrangements have #23 contacts.

- Aerospace-grade rectangular PCB connector with high speed size 8 quadraxial contacts
- 1–5 data ports
- Rugged duo-lobe aluminum shell
- Environmental

INSERT ARRANGEMENTS

Thermoplastic Insert	Grounded All-Aluminum	No. of Contacts	
		Quadrax	#23
A-1P1	A-1G1	1	–
A-3P1		1	2
B-23P1		1	22
B-2P2	B-2G2	2	–
B-6P2		2	4
C-24P2		2	22
C-3P3	C-3G3	3	–
C-9P3		3	6
D-27P3		3	24
D-4P4	D-4G4	4	–
D-12P4		4	8
E-5P5	E-5G5	5	–
E-15P5		5	10
E-45P3		3	42

RATINGS

- Voltage (DWV): #23 100 VAC, ungrounded quadrax to shell 1800 VAC
- Current: #23 1A
- Operating temperature: -65 to +150 °C
- Durability: 500 mating cycles
- Shock: 300 g
- Vibration: 20 g random

CONSTRUCTION

- #23 Contacts: Copper alloy, gold over nickel finish, stainless steel hood
- Quadrax contact: Copper alloy, gold over nickel finish. Insulators are high performance thermoplastic.
- Shell: Aluminum
- Insulator: High performance thermoplastic
- Encapsulant: Epoxy
- Hardware: Stainless steel, passivated

HOW TO ORDER

Sample Part Number

Basic Part Number	792-023P	792-023P	D-4P4	M	E	P	B
Shell Size-Insert Arr.	See "Insert Arrangements" Table						
Shell Finish	M Electroless Nickel MT Nickel / PTFE N Olive Drab Cadmium TZ Tin-Zinc ZR Black Zinc-Nickel						
EMI Spring	E EMI Spring N No EMI Spring						
Hardware Option Table 1	N No Hardware <i>Threaded holes</i> B Guide Pins <i>For blind mating</i> P Female Jackposts						
Polarization Key Option	Enter Letter Designator for Position A, B, C, D, E, F, G, H, J, or K per Mod Code 1104 (see page C-8 for details) Omit for none						


TABLE 1 HARDWARE OPTION

N No Hardware Threaded Hole 10-32 UNF-2B .150 (3.81) min. depth	P Female Jackpost 8-32 UNC-2B	B Female Guide Bushing
---	---	--

Application Note

Polarization Key Positions

See Mod Code 1104 pg. C-8 for details



MICRO-CRIMP RECTANGULAR CONNECTORS


Series 792 High-Speed



792-023


PCB Receptacle, 90° Tails, Quadrax

- ◆ Quadrax PC tail contacts
- ◆ 90° mounting
- ◆ Pin contacts



Shell Size	A Max		B ± .005 (0.1)		C Max		D ± .005 (0.1)		E ± .002 (0.05)	
	in	mm	in	mm	in	mm	in	mm	in	mm
A	1.455	36.96	1.075	27.31	.690	17.53	1.075	27.31	.725	18.42
B	1.830	46.48	1.450	36.83	1.065	27.05	1.450	36.83	1.100	27.94
C	2.205	56.01	1.825	46.36	1.440	36.58	1.825	46.36	1.475	37.47
D	2.580	65.53	2.200	55.88	1.815	46.10	2.200	55.88	1.850	46.99
E	2.955	75.06	2.575	65.41	2.190	55.63	2.575	65.41	2.225	56.52

PANEL CUTOUT



MICRO-CRIMP RECTANGULAR CONNECTORS

Series 792 High-Speed










792-023

PCB Receptacle, 90° Tails, Quadrax

- ◆ Quadraxial PC tail contacts
- ◆ 90° mounting
- ◆ Pin contacts

PCB FOOTPRINTS FOR 792-023 CONNECTOR

⚠ PCB hole patterns are shown for the **component mounting side** of the circuit board, looking through the connector.



MICRO-CRIMP RECTANGULAR CONNECTORS

Series 792 High-Speed




792-023


PCB Receptacle, 90° Tails, Quadrax

- ◆ Quadraxial PC tail contacts
- ◆ 90° mounting
- ◆ Pin contacts


PCB FOOTPRINTS FOR 792-023 CONNECTOR




C-9P3




C-24P2




D-4P4 D-4G4




D-12P4




D-27P3



E-5P5 E-5G5



E-15P5



E-45P3