

MICRO-CRIMP RECTANGULAR CONNECTORS

Series 793 Dual-Bay



793-006

Plug, Panel Mount, Horizontal, Straight PCB Tails

- ◆ Rear panel mounting
- ◆ Socket contacts
- ◆ PCB tails




Dual bay, blind mating, PC tails. Space-saving 793-006 connector features high-density and high current capabilities, saves size and weight compared to legacy rack-and-panel types. Connector has factory-installed straight PC tail contacts. PC tails are encapsulated with epoxy potting compound. Panel mounting holes and PCB mounting holes have stainless steel self-locking threaded inserts. Connectors become non-scoop proof at parallel horizontal angles of entry from 16°–47°.

- Aerospace-grade rectangular rack-and-panel connector
- Dual bay horizontal
- Environmental
- Epoxy-sealed PCB tails


INSERT ARRANGEMENTS

Identification numbers are mating face of plug (socket) connector




102

102 #23 Contacts




4W4

4 #8 Contacts



17W17

17 #16 Contacts




68W2

66 #23, 2 #12 Contacts




40W4

36 #23, 4 #12 Contacts




74W4

70 #23, 4 #16 Contacts



7W7

7 #12 Contacts



19W6

13 #23, 6 #12 Contacts

HOW TO ORDER

Sample Part Number	793-006S	A17P17	B102	M	G	A	B
Basic Part Number	793-006S	Plug, Socket Contacts					
Bay "A" Insert Arr.	A102 A4P4 A17P17	A68P2 A40P4 A74P4	A7P7 A19P6				
Bay "B" Insert Arr.	B102 B4P4 B17P17	B68P2 B40P4 B74P4	B7P7 B19P6				
Shell Finish	M Electroless Nickel MT Nickel / PTFE N Olive Drab Cadmium TZ Tin-Zinc ZR Black Zinc-Nickel						
Hardware Option Table 1	P Female Jackposts G Guide Pins For blind mating B Guide Bushings For blind mating						
PC Tail Length	A .125 (3.2) B .250 (6.4)						
Polarization Key Option	Enter Letter Designator for Position A, B, C, or D per Mod Code 1502 (see page D-5 for details) Omit for none						

TABLE 1 HARDWARE OPTION

P Female Jackpost	G Guide Pin	B Guide Bushing

RATINGS

- Voltage (DWV): size 23 contacts 750 VAC, size 8, 12 and 16: 1800 VAC
- Current: #23 5A, #16 13A, #12 23A, #8 46A
- Operating temperature: -65 to +150 °C
- Durability: 500 mating cycles
- Shock: 300 g
- Vibration: 20 g random
- Altitude immersion: 75,000 feet
- Ingress protection: IP67

CONSTRUCTION

- Socket Contacts: Copper alloy, gold over nickel finish. Stainless steel hood.
- Shell: Aluminum
- Insulator: High performance thermoplastic
- Encapsulant: Epoxy
- Hardware: Stainless steel

MICRO-CRIMP RECTANGULAR CONNECTORS

Series 793 Dual-Bay


SERIES
793
Dual-Bay

793-006


Plug, Panel Mount, Horizontal, Straight PCB Tails

- ◆ Rear panel mounting
- ◆ Socket contacts
- ◆ PCB tails

SERIES 793 DUAL-BAY




PANEL CUTOUT FOR REAR MOUNTING



Application Note

Polarization Key Positions

See Mod Code 1502 pg. D-5 for details



MICRO-CRIMP RECTANGULAR CONNECTORS

Series 793 Dual-Bay




793-006

Plug, Panel Mount, Horizontal, Straight PCB Tails


- ◆ Rear panel mounting
- ◆ Socket contacts
- ◆ PCB tails

PCB FOOTPRINTS FOR 793-006 CONNECTOR




PCB hole patterns are for the **connector mounting side** of the circuit board.


Identification numbers are for P/N 790-006 plug with socket contacts.




SERIES 793 DUAL-BAY




102




4P4




17P17




68P2




40P4



74P4



7P7



19P6