


Eye-Beam™ GMA
M83526 type In-Line Plug-to-Plug cable assembly



| REFERENCE PART NUMBER* | | | | | | | |
|------------------------|--|------------|-----------|-----------|-----------|-------------|-----------|
| Sample Part Number | FA03939 | -60 | -1 | -3 | -4 | -100 | -3 |
| Basic number | GMA Fiber Optic cable | | | | | | |
| GMA Connector Type | -60 = Plug, hermaphroditic, in-line | | | | | | |
| Fiber Type | -1 = Singlemode 9/125 -2 = Multimode 50/125 -3 = Multimode 62.5/125 | | | | | | |
| Wavelength | -1 = Multimode 850 nm -2 = Multimode 1300 nm -3 = Singlemode 1310 nm -4 = Singlemode 1550 nm | | | | | | |
| Number of Fibers | -2 = 2 channel -4 = 4 channel | | | | | | |
| Length | Overall length in feet | | | | | | |
| Reel Type | -1 = Metal reel -2 = Metal reel with castors -3 = Wooden reel -4 = Plastic reel -5 = Manpack reel -6 = Customer specified (Omit for no reel) | | | | | | |

* Use this part number for reference only. A unique Glenair part number will be assigned to your cable order



RUGGED FIELD / EXPANDED BEAM

OPTICAL PERFORMANCE

- <1.0dB at 850nm multimode
- <1.5dB at 1310nm singlemode

