


Keyed Jumper Assembly FO04309 GHD Fiber Optic Test Probe

Fiber optic test probe for fast and easy optical analysis of installed fiber optic systems

Fiber Size	
Symbol	Size
E	Singlemode 9.3/125
F	Singlemode 5.8/125
G	Singlemode 7.5/125

HOW TO ORDER					
Sample Part Number	FO04309	E	E	3	G
Basic Number	FO04309 GHD Fiber Optic Test Probe				
Fiber Size	See Fiber Size table				
Connector Type:	A = ST Connector B = FC Connector C = SC Connector D = LC Connector		E = FC/APC Connector F = SC/APC Connector G = LC/APC Connector		
"A" Length	(in meters)				
Adapter Style	G = GHD				

Optical insertion loss ≤ 1.0 dB @ 1310 nm wavelength.
Glenair Fiber Optic Test Probe U.S. Patent Number 5,960,137.



NOTE

- "APC" physical contact polish to be IAW Glenair manufacturing procedure AWS-A040-F
- For use with the following test probe adapters:
180-131: GHD (180-122)

Fiber optic polishing tool for GHD style termini fiber optic test probes



HOW TO ORDER		
Sample Part Number	182-018	W
Basic Number	018 = Fiber optic polishing tool for GHD style termini fiber optic test probes	
Polish	W = Wet Polish Supplied with V-Grooves (Omit for Dry Polish)	

NOTE

- Polishing puck is for PC polish only. For APC Glenair recommends autopolish, consult factory for more information
- Polishing tool is designed for use with the following Glenair termini:
181-047 (Pin, size 18 terminus)
181-056 (Pin, size 18 terminus)

KITS AND TOOLS