

ABC 54705 Replacement Fiber Optic Test Probe Jumper


Fiber optic test probe for fast and easy optical analysis of installed fiber optic systems

Fiber Size	
Symbol	Size
A	100/140 μm
B	62.5/125 μm
C	50/125 μm
D	200/230 μm
E	Singlemode 9.3/125
F	Customer Defined
G	SM 5.8/125 M/F DIA. .21na
H	SM 7.5/125 M/F DIA. .17na

HOW TO ORDER					
Sample Part Number	ABC 54705	A	A	3	C
Basic Number	ABC 54705 Replacement Fiber Optic Test Probe Jumper				
Fiber Size	See Fiber Size table				
Connector Type:	A = ST Connector F = LC Connector B = FC Connector G = SC/APC Connector C = SC Connector H = M29504/04 Pin D = FC/APC Connector J = M29504/05 Socket E = Customer Defined				
"A" Length	In meters				
Polish	F = Flat Polish C = Concave Polish (Probe end only. Omit for standard "PC" physical contact polish)				

Optical insertion loss ≤ 1.0 dB @
850 or 1300 nm wavelength.
Glenair Fiber Optic Test Probe U.S.
Patent Number 5,960,137.

Standard Tolerance	
Length	Tolerance
5 in, up to 2 ft	+1/-0 in
Over 2 ft, up to 10 ft	+3/-0 in
Over 10 ft, up to 50 ft	+6/-0 in
Over 50 ft, up to 100 ft	+1/-0 ft
Over 100 ft	+2/-0 ft



Fiber optic polishing tool for fiber optic test probes



HOW TO ORDER		
Sample Part Number	182-002	W
Basic Number	182-002	
Polish	W = Wet Polish Supplied with V-Grooves (Omit for Dry Polish)	