

## Product selection guide



### ABOUT MIL-DTL-38999 SERIES III TYPE FIBER OPTIC PRODUCTS

Glenair's complete line of multi-channel MIL-DTL-38999 Series III Type fiber optic products includes qualified size 16 MIL-PRF-29504 /4 and /5 precision ceramic termini, and commercial large-core and jewel size 16 termini, as well as high-density size 20 termini. Tight-tolerance fiber optic provides repeatable, reliable optical performance. Connectors, backshells, and accessories IAW MIL-DTL-38999 Series III (Glenair SuperNine®) are available in metal and composite versions.

Product No.	Description	Page No.
<b>MIL-PRF-29504 TYPE FIBER OPTIC TERMINI</b>		
<b>181-001</b>	M29504/05 Type Socket Terminus, Size 16	B-4
<b>181-002</b>	M29504/04 Type Pin Terminus, Size 16	B-5
<b>181-009</b>	M29504/05 Fiber Optic Socket Terminus, Size 16	B-6
<b>181-010</b>	M29504/04 Fiber Optic Pin Terminus, Size 16	B-7
<b>181-035</b>	Large-core Fiber Socket Terminus, Size 16	B-8
<b>181-036</b>	Large-core Fiber Pin Terminus, Size 16	B-9
<b>181-052</b>	Jewel Pin Terminus, Size 16	B-10
<b>181-053</b>	Jewel Socket Terminus, Size 16	B-11
<b>187-019/187-029</b>	Dust Caps for Pin and Socket Termini, Size 16	B-12
<b>181-048</b>	Dummy Sealing Plug, Size 16	B-13
<b>180-076</b>	Fiber Optic Splice	B-13
<b>181-065</b>	Pin Terminus, Size 20	B-14
<b>181-066</b>	Socket Terminus, Size 20	B-15
<b>187-266</b>	Dust Caps for Pin and Socket Termini, Size 20	B-12
<b>SINGLE CHANNEL CONNECTORS FOR USE WITH MIL-PRF-29504 TYPE TERMINI</b>		
<b>180-076</b>	Fiber Optic Splice, Size 16	B-13
<b>180-071 (-6)</b>	Single Channel Plug Connector	B-16
<b>180-071 (-3)</b>	Single Channel Square Flange Wall Mount Receptacle Connector	B-17
<b>180-071 (-4)</b>	Single Channel Jam Nut Mount Receptacle Connector	B-18
<b>189-055</b>	Environmental Backshell for Series 180-071 Connectors	B-19
<b>189-047</b>	Plug and Receptacle Protective Cover for Series 180-071 Connectors	B-20
<b>MIL-DTL-38999 SERIES III TYPE FIBER OPTIC CONNECTORS AND THREADED PROTECTIVE COVERS</b>		
<b>180-091 (06)</b>	Plug Connector	B-22
<b>180-091 (05)</b>	In-Line Receptacle Connector	B-24
<b>180-091 (08)</b>	Jam Nut Mount Receptacle Connector	B-26
<b>180-091 (H7)</b>	Square Flange Wall Mount Receptacle Connector, Round holes (std.)	B-28
<b>180-091 (S7)</b>	Square Flange Wall Mount Receptacle Connector, Slotted holes	B-30
<b>180-091 (T7)</b>	Square Flange Wall Mount Receptacle Connector, Threaded holes	B-32
<b>BACKSHELLS AND ACCESSORIES</b>		
<b>660-023/024 • 660-049/050</b>	Protective Covers	B-34
<b>667-448</b>	ProSeal™ Threaded-Closure Seal, Full Environmental	B-37
<b>189-016</b>	Self-Locking Banding Backshell with Strain Relief	B-38
<b>189-037</b>	Self-Locking Banding Backshell with Strain Relief and Bend Restrictor	B-40
<b>377-014</b>	Composite Thermoplastic Backshell, FiberCon	B-42
<b>377-040</b>	Composite Backshell with Optional Strain Relief Adapter, FiberCon	B-44
<b>377-041</b>	Composite Backshell with Helical Conduit Adapter, FiberCon	B-46
<b>189-038</b>	Composite Backshell with Helical Conduit Adapter	B-48
<b>712-416</b>	Composite Backshell with Helical Conduit Adapter for PEEK Only	B-50
<b>630-015</b>	Cable Bulkhead Adapter with Strain Relief and Braid Sock	B-52
<b>ASAP FIBER OPTIC CABLE SETS</b>		
<b>FO1000 thru FO1005</b>	Fast-Turnaround Overmolded Cables, Conduit Assemblies, Field-Repairable Backshell Assemblies, and Inside-the-Box Pigtail Assemblies	B-54-B-65

#### DIMENSIONAL NOTES

- Catalog dimensions are subject to change without notice. Consult Glenair engineering for a controlled-release sales drawing
- Metric dimensions appear in parentheses in diagrams and tables, based on 1 inch = 25.4 mm, for reference only.
- Unless otherwise specified, the following other dimensional tolerances apply:
  - .xx = ± .03 (0.8) • .xxx = ± .015 (0.4) • Angles = ± 5°