


## 181-043 MIL-PRF-29504/18 and /20 Type Termini 181-078 Dummy terminus



HOW TO ORDER NGCON MIL-PRF-29504 TYPE TERMINI						
Part Number Non-Keyed	Part Number Keyed	ØA (Micron)	Fiber Type	Typical Fiber Size Core/Cladding/Coating (Micron)	Ref. M29504/18 Non-Keyed	Ref. M29504/20 Keyed
181-043-1250C	181-043K-1250C	125.0	SM	9/125	M29504/18-01Y	M29504/20-01Y
181-043-1255C	181-043K-1255C	125.5	SM	9/125	M29504/18-02Y	M29504/20-02Y
181-043-1265C	181-043K-1265C	126.0	SM	9/125	M29504/18-03Y	M29504/20-03Y
181-043-126C	181-043K-126C	126.0	MM	50/125, 62.5/125	M29504/18-26Y	M29504/20-26Y
181-043-127C	181-043K-127C	127.0	MM	50/125, 62.5/125	M29504/18-27Y	M29504/20-27Y
181-043-142C	181-043K-142C	142.0	MM	100/140	M29504/18-42Y	M29504/20-42Y
181-043-145C	181-043K-145C	145.0	MM	100/140	M29504/18-45Y	M29504/20-45Y
181-043-156C	181-043K-156C	156.0	MM	62.5/125/155	M29504/18-56Y	M29504/20-56Y
181-043-157C	181-043K-157C	157.0	MM	62.5/125/155	M29504/18-57Y	M29504/20-57Y
181-043-173C	181-043K-173C	173.0	MM	100/140/172	M29504/18-73Y	M29504/20-73Y
181-043-175C	181-043K-175C	175.0	MM	100/140/172	M29504/18-75Y	M29504/20-75Y

SM = Singlemode • MM = Multimode • Consult factory for additional sizes and QPL status.



ACCESSORIES	
Part No.	Description
181-043-C	Crimp Sleeve, Ø2.4mm Max Jacket
182-012	Crimp tool
182-013	Insertion tool, straight
182-014	Insertion tool, 90°
182-021	Hand polishing tool
182-025	Removal tool

### MATERIAL AND FINISH / NOTES

- Ferrule: Zirconia Ceramic
- Terminus Assembly: Stainless steel/passivate
- Retention Clip: Spring alloy
- Spring: Stainless steel/passivate
- Seal: Elastomeric rubber
- Crimp Sleeve: Stainless steel/passivate
- Crimp sleeve is supplied with terminus assembly, and may be ordered separately (see accessories table).

HOW TO ORDER NGCON DUMMY TERMINUS	
181-078	M29504/19-type rear-release dummy terminus for NGCON

