






Geo-Marine® Special Purpose, Custom Application Connector Capabilities



Quick Selection Guide

	High-Pressure Environmental Plug with Quick Disconnect Lanyard 227-015	D-2
	High-Pressure Environmental Cable Plug with Wire Mesh Cable Grip 227-158	D-3
	High-Pressure Environmental In-Line Gender Changer 227-152	D-5
	High-Pressure Environmental Square Flange Wall-Mount Gender Changer 940-016	D-6
	High-Pressure Environmental Sav-Con® Connector Saver (Non Scoop-Proof) 940-014	D-8
	High-Pressure Environmental Jam Nut Mount Sav-Con® Connector Saver 940-015	D-9
	High-Pressure Environmental Sav-Con® Connector Saver (Scoop-Proof) 940-025	D-10
	Hermetic Receptacle With Triangular Flange Mount 227-162H	D-12
	High-Pressure Environmental Box Mount Plug with Circular Flange 227-163	D-13
	Stainless Steel Harsh Environment Connector Receptacle Assembly 257-003	D-15
	Stainless Steel Harsh Environment Receptacle Assembly with PCB Contacts 257-005	D-18
	Stainless Steel Harsh Environment Connector Receptacle Assembly 257-007	D-19
	Stainless Steel Harsh Environment Connector Receptacle Assembly 257-012	D-22
	Flange Mount and Weld Mount Stainless Steel Connector Receptacle Assemblies 257-163 and 257-164	D-23
	Stainless Steel Plug and Receptacle Assemblies 257-165 and 257-166	D-25
	10KPSI Series Underwater Interconnect Assemblies	D-27