



HDSTACKER™

High-density, solder-free, rugged board-to-board stackable connectors


Mission-critical board-to-board connector applications demand fail-safe signal integrity as well as rugged and reliable harsh-environment performance. The HD Stacker™ brings Glenair innovation to stacking board-to-board connectors with several significant design improvements: Ultra high-density .0625" Chevron Contact System provides 55% more contacts per connector size, or a 31% size reduction for the same number of contacts as compared to current industry solutions. Polarized connector bodies and available polarized guide pins prevent accidental mismatching. The solder-free press-fit compliant pin contacts are removable, repairable, and available in custom lengths. HD Stacker™ connectors may also be ordered with pre-wired cable or flex jumper terminations. High-speed signal integrity test reports are available on the Glenair website. Choose HD Stacker™ for the ultimate in high-density, rugged board-to-board stackable connector performance.

- High-density .0625" pitch Chevron Contact System
- PCIe 3.0 capable
- Performance up to 10.5 Gbps
- Polarized insulator and hardware options
- Solder free "eye of the needle" compliant tail for press fit installation
- Meets RoHS and REACH requirements
- Available wired / flex jumpers
- Available between-board spacers up to 1 inch


HD STACKER™ FOR MISSION-CRITICAL BOARD-TO-BOARD APPLICATIONS




Solder-free press-fit (compliant pin) board mounting



.0625" pitch contact spacing: highest available density



Polarized shells and keyed guide pin hardware prevent mis-mating



Controlled signal integrity for differential applications (test reports available)