


Dummy contact for high density contacts

DUMMY CONTACT FOR HD CONTACTS

How to Order			
Sample Part Number	680-120	-20HD	B
Series	680-120 = Dummy contact		
Dash No.	See Table		
Boot Option	B = Boot supplied with assembly (Omit for none) (Dash No -8 only)		



Dash No.	Color Code	Ø A		Ø B		C Max		Extraction Tool	Standard Order Quantity
		in.	mm	in.	mm	in.	mm		
-8	Green	0.315	8.00	0.218	5.54	1.46	37.08	M81969/14-06	100
-20HD	Brown	0.084	2.13	0.040	1.02	1.18	29.97	809-203	1000
-22HD	Bone	0.054	1.37	0.027	0.69	1.18	29.97	859-150	1000

Material and Finish

Material: Molded plastic (200°C minimum temp limit)

Dummy contacts are designed to seal the unused crimp removable contact cavities of hd contacts.

Dummy contacts to be bagged and tagged.

Special rates may apply for non-standard order quantities. See table. Not applicable to bag and tag quantities.