

A

Performance Specifications		
Description	Requirement	Procedure
Current Rating	Contact	EIA-364-70 Method 1 IEC-60512-5 Test 9b
	Size	
	8	
	20	
Shell-to-Shell Resistance (connectors with ground springs)	Max	EIA-364-83 IEC-60512-2-6 Electroless nickel plated connectors.
	Current	
	40	
	7.5	
Shielding Effectiveness	2.5 milli-volt drop maximum	EIA-364-66 IEC-60512-23-3 Pin Connector with Optional Grounding Spring, Electroless nickel plated shells
	Frequency	
	MHz	
	Min	
	Attenuation (dB)	
	100	
	200	
	300	
	400	
	800	
	1000	
	1500	
	2000	
	3000	
	4000	
	6000	
	10000	