

M1222 Bolt

SPECIFICATIONS

- Materials and design IAW MIL-DTL-1222

BOLT: HOW TO ORDER										
Sample Part Number	M1222	R	N	6	C	2	12	SD	N	N
Product Series	MIL-DTL-1222 Bolt									
Fastener Type	R = Hex Cap Screw									
Bearing Surface	N = Does Not Apply									
Nominal Diameter	in 1/16ths of an inch (e.g. 6 = .375")									
Thread Type	C = Coarse (UNC)									
Thread Class	2 = Class 2A									
Nominal Length	in 1/16ths of an inch (e.g. 12 = .75")									
Material Type	SD = Cold-Worked Grade 316									
Locking Element	N = No Locking Element									
Coating	N = No Coating									

