

121-193


Annular Polymer-Core Convulsed Tubing  
with Double External Braid and Jacket



Series 72  
Annular Tubing

For environmental EMI/RFI applications with high dB shielding requirements

How To Order




B

Dash No	A Inside Dia		B Outside Dia
	Min	Max	Max
06	.17 (4.3)	.19 (4.8)	.57 (14.5)
09	.24 (6.1)	.28 (7.1)	.67 (17.0)
12	.33 (8.4)	.37 (9.4)	.77 (19.5)
14	.40 (10.1)	.44 (11.2)	.84 (21.3)
16	.45 (11.4)	.50 (12.7)	.91 (23.1)
20	.57 (14.5)	.62 (15.7)	1.02 (25.9)
24	.69 (17.5)	.75 (19.1)	1.19 (30.2)
28	.81 (20.6)	.87 (22.1)	1.33 (33.8)
32	.93 (23.6)	1.00 (25.4)	1.45 (36.8)
40	1.18 (30.0)	1.25 (31.8)	1.69 (42.9)
48	1.43 (36.3)	1.50 (38.1)	1.96 (49.8)
52	1.56 (39.6)	1.63 (41.4)	2.10 (53.3)

Y	Kynar/Thermally stabilized
V	PVDF/Not thermally stabilized
S	G-FLEX Siltem/Medium duty - natural color only

T	Tin/Copper
C	Stainless Steel
N	Nickel Copper
L	ArmorLite™
D	Dacron
M	Nomex
E	AmberStrand® 100%
F	AmberStrand® 75%/25%

N	Neoprene
H	Hypalon
E	EPDM
V	Viton
B	Duraelectric, black
G	Bluejacket, Gray
TN	Duraelectric, Desert Tan



Dash No.	Max Length Per Pkg.
09& 12	200 ft (60m)
16 - 52	100 ft (30m)

Packaging

121-193 braided and jacketed conduit is typically supplied in 50 foot lengths. Longer lengths are available—consult factory for additional information. Unless otherwise specified, Glenair packages optimal lengths of product based on weight, size, and commercial carrier specifications. If necessary, consult factory for additional information on package weight restrictions.