


MIL-DTL-26500 TYPE Glass Sealed Hermetic Receptacles



230-036

MS27034H*B*** Type solder flange mount, bayonet coupling

HOW TO ORDER						
Sample Part Number	230-036	Z1	12	-3	P	6
Basic Part Number	230-036 Solder flange mount, bayonet coupling					
Material / Finish	FT = Carbon steel / tin plated Z1 = Stainless steel / passivated ZL = Stainless steel / nickel finish					
Shell Size	8, 10, 12, 14, 16, 18, 20, 22, 24					
Insert Arrangement	Per MIL-STD-1554					
Contact Type	P = Pin, solder cup X = Pin, eyelet					
Alternate Key Position	6, 7, 8, 9, 10 (Omit for normal)					



MIL-DTL-26500 TYPE Glass Sealed Hermetic Receptacles



230-036

MS27034H*B*** Type solder flange mount, bayonet coupling

TABLE I: SHELL SIZE, CONNECTOR DIMENSIONS AND PANEL CUT-OUT

Shell Size	Ø A	Ø C Max	Ø D Shell I.D.	Ø E Resilient Insert	Ø F	Ø G Max	Panel Cut-Out Ø GG
8	.725/.685 (18.4/17.4)	.437 (11.1)	.433/.428 (11.0/10.9)	.312 (7.9)	.536/.531 (13.6/13.5)	.561 (14.2)	.452/.442 (11.5/11.2)
10	.860/.820 (21.8/20.8)	.562 (14.3)	.535/.530 (13.6/13.5)	.388 (9.9)	.659/.654 (16.7/16.6)	.696 (17.7)	.577/.567 (14.7/14.4)
12	1.065/1.025 (27.1/26.0)	.750 (19.1)	.705/.700 (17.9/17.8)	.558 (14.2)	.829/.824 (21.1/20.9)	.875 (22.2)	.765/.755 (19.4/19.2)
14	1.110/1.070 (28.2/27.2)	.812 (20.6)	.774/.769 (19.7/19.5)	.627 (15.9)	.898/.893 (22.8/22.7)	.935 (23.7)	.827/.817 (21.0/20.8)
16	1.230/1.190 (31.2/30.2)	.937 (23.8)	.901/.896 (22.9/22.8)	.754 (19.2)	1.025/1.020 (26.0/25.9)	1.062 (27.0)	.952/.942 (24.2/23.9)
18	1.360/1.320 (34.5/33.5)	1.062 (27.0)	1.007/1.002 (25.6/25.5)	.860 (21.8)	1.131/1.126 (28.7/28.6)	1.187 (30.1)	1.077/1.067 (27.4/27.1)
20	1.495/1.455 (38.0/37.0)	1.182 (30.0)	1.132/1.127 (28.8/28.6)	.985 (25.0)	1.256/1.251 (31.9/31.8)	1.312 (33.3)	1.197/1.187 (30.4/30.1)
22	1.610/1.570 (40.9/39.9)	1.312 (33.3)	1.257/1.252 (31.9/31.8)	1.110 (28.2)	1.381/1.376 (35.1/35.0)	1.437 (36.5)	1.327/1.317 (33.7/33.5)
24	1.745/1.705 (44.3/43.3)	1.432 (36.4)	1.382/1.377 (35.1/35.0)	1.235 (31.4)	1.506/1.501 (38.3/38.1)	1.562 (39.7)	1.447/1.437 (36.8/36.5)

TABLE II: CONTACTS

Contact Size	Contact Type	AA	ØØ BB	ØØ CC Min	DD	FF Max
12	Cup	--	.150 (3.8)	.112 (2.8)	.200 (5.1)	.400 (10.2)
12	Eyelet	.035 (0.9)	--	.112 (2.8)	--	.400 (10.2)
16	Cup	--	.103 (2.6)	.069 (1.8)	.125 (3.2)	.400 (10.2)
16	Eyelet	.025 (0.6)	--	.069 (1.8)	--	.400 (10.2)
20	Cup	--	.077 (2.0)	.042 (1.1)	.080 (2.0)	.330 (8.4)
20	Eyelet	.015 (0.4)	--	.042 (1.1)	--	.330 (8.4)

NOTES

- To be identified with manufacturer's name, part number and date code, space permitting.
- Material/Finish:
Shell*:
Z1 - Stainless steel/passivated.
FT - Carbon steel/tin plated.
• Contacts - 52 Nickel alloy/gold plated.
• Bayonets - Stainless steel/passivated.
• Seals - fluorosilicone elastomer/N.A.
• Insulation - Glass/N.A.
- Glenair 230-036 will mate with any QPL MIL-DTL-26500, MS24266 and MS27615 series bayonet coupling plug of same size, keyway and insert polarization. Performance:
• Hermeticity - $<1 \times 10^{-7}$ cc He/sec @ 1 atmosphere differential.
• Dielectric withstanding voltage - Consult factory or MIL-STD-1554.
• Insulation resistance - 5000 megohms min. @ 500VDC.
- Consult factory and/or MIL-STD-1554 for arrangement, keyway, and insert position options.
- Metric Dimensions (mm) are indicated in parentheses.