



Glenair IPT Series Bayonet-Lock Signal Connectors (MIL-DTL-26482 Series I) Materials and Finishes

MATERIALS	
COMPONENT	MATERIAL
Shells	Aluminum Alloy Shells Stainless Steel Coupling Pins Stainless Steel Spring
Inserts (Temperature Range)	High Insulation Synthetic Rubber (Chloroprene): -55°C/+125°C
Contacts	Copper Alloy with Gold Plating Over Nickel

STANDARD MATERIAL & FINISH OPTIONS					
Property	RoHS				Not RoHS
	Alum/Black Non Conductive	Alum/Black Conductive	Alum/Electroless Nickel	Unplated/Marine Bronze	Alum/Cadmium Olive Drab
	F6	F7	F11	MB	G3
Temperature Range	-55°C + 125°C	-55°C + 175°C	-55°C + 125°C	-55°C + 200°C	-55°C + 125°C
Salt Spray Hours	500	500	48	1000	500
Electical Conductivity	NO	Good	Very Good	Very Good	Very Good

TABLE II: MODIFICATION CODES

CONTACT OPTIONS	
Sym	Description
B0	Connector Without Contacts (Only for crimp version)
FINISH OPTIONS	
Sym	Description and RoHS compliant
F6	Black Electrodeposited Paint
F7	Black Zinc Nickel
F11	Electroless Nickel
MB	Marine Bronze
Omit for standard version (Cadmium Olive Drab Finish)	