

HIGH-VOLTAGE kV Seal™ Contact Assemblies



GHV-005 kV Seal Housing

kV SEAL™ CONTACT ASSEMBLIES

HOW TO ORDER

Sample Part Number	GHV-005	-00	NF	-A
Series	GHV-005 = kV Seal Housing			
Connector Style	06 = Plug 00 = Receptacle Sq Wall Mount 05 = In-Line Receptacle			
Material/Finish	See Material/Finish Table			
Contact Style	A = Pin, Less Contact B = Socket, Less Contact			

MATERIAL/FINISH TABLE

Class	Material	Finish
NF	Aluminum Alloy	Cad/O.D. Over Electroless Nickel (500 Hour Salt Spray)
ME		Electroless Nickel (48 Hour Salt Spray)
MA		Electroless Nickel, Matte (48 Hour Salt Spray)
MN		Tri-Nickel Alloy (Mega-Nickel, 1000 Hour Salt Spray)
MT		Nickel, PTFE
TZ		Tin-Zinc
ZN		Zinc Nickel, Olive Drab
ZR		Zinc Nickel-Black
Z1	SST	Passivate
ZL		Electrodeposited Nickel
TD	Titanium	Natural - No Plate
AB	Marine Bronze	None (Clean Only)


NOTES

- Connectors are contact specific. The contacts are not interchangeable, between pin and socket.
- Connector accepts GHV-003 contacts only
- kV seal contacts not included


MATERIAL / FINISH

- Shell, barrel, coupling nut - see table
- Seals- fluoroelastomer blend / N.A.

GHV-005-06 (PLUG)



GHV-005-00 (RECEPTACLE SQ WALL MOUNT)



GHV-005-05 (IN-LINE RECEPTACLE)

