

High-Speed HiPer-D® Connectors



280-082P pin connector with size #8 coax, twinax, quadrax and El Ochito® (octaxial) contacts



- Rugged machined one-piece shell
- Coax, twinax, quadrax, and El Ochito® contacts
- Easy contact installation and removal
- Fits panel footprint of M24308 D-Sub products

Technical Data

Specifications

- Operating temperature: -65 °C. to +200 °C.
- Durability: 500 mating cycles
- Shock: EIA-364-27 condition E
- Vibration: EIA-364-28 condition IV
- Humidity: EIA-364-31 condition 4
- Salt spray: EIA-364-26 condition B
- Maximum Mating Force:
shell size 1: 10 lbs.
shell size 2: 17 lbs.
shell size 3: 28 lbs.
shell size 4: 39 lbs.

Construction

- Shell: aluminum alloy
- Ground spring: beryllium copper, nickel plated
- Retainers: aluminum alloy
- Screws: stainless steel, passivated


Ordering Information

Sample Part Number	280-082P	2Q2	ME	G	N	-05
Basic Part Number	280-082P					
Shell Size- Insert Arrangement	See Table 1					
Shell Finish (See Section A for Additional Finishes)	ME = Electroless Nickel MT = Nickel-PTFE Z2 = Gold over Electroless Nickel JF = Yellow Chromate over Cadmium					
Ground Spring	G = Supplied with EMIGround Spring N = No Ground Spring					
Mating Hardware (See Table 3 for details)	N = No Hardware (Through-Hole) P = #4-40 Female Jackpost L = Captive Jackscrew, Hex Head, Low Profile K = Slot Head Jackscrew, Extended Length S = Screwlock, Male, Hex Head, Low Profile T = Screwlock, Male, Slot Head, Extended Length					
Hi-Speed Contact Option	See Table 2 for contact dash numbers. Omit if ordered less contacts.					

Table 1
Shell Size – Insert Arrangement

Shell Size	No of Contacts	Coax	Differential Twinax	Concentric Twinax	Quadrax	Ochito (Octo-Ax)	Less Contacts
1	1	1C1	1D1	1T1	1Q1	1E1	1W1
2	2	2C2	2D2	2T2	2Q2	2E2	2W2
3	3	3C3	3D3	3T3	3Q3	3E3	3W3
3	4	3C4	3D4	3T4	3Q4	3E4	3W4
4	5	4C5	4D5	4T5	4Q5	4E5	4W5

Contact Arrangements



Cavity identification is shown for the mating face of pin connector.

280-082P pin connector with size #8 coax, twinax, quadrax and El Ochito® (octaxial) contacts

Table 2
Size 8 Pin Contacts for 280-082P Connectors

Contact Type	Dash No.	Cable Type	Ref. Contact Part Number*
Coax (1C1, 2C2, 3C3, 3C4, 4C5)	-01	RG316DS	852-110-01
	-02	RG316	852-110-02
	-03	RG142, RG400	852-110-03
Concentric Twinax (1T1, 2T2, 3T3, 3T4, 4T5)	-01	0024A0024 (TE) GSC-03-81416-00 (Gore)	853-011
	-02	M17/176-00002	853-003-08-625
Differential Twinax (1D1, 2D2, 3D3, 3D4, 4D5)	-01	RCN8945 (Gore)	853-014-01
	-02	GSC-03-83971-00 (Gore)	853-014-02
	-03	10612 (TE)	853-014-03
	-04	0024A0024 (TE)	853-014-04
	-05	M17/176-00002 5M2022-003	853-014-05
	-06	1350SB (Belden)	853-014-06
	-07	2525B0524 (TE)	853-014-07
Quadrax (1Q1, 2Q2, 3Q3, 3Q4, 4Q5)	-01	NF26Q100-01 (Carlisle)	854-001-01
	-02	E51424 (PIC) NF24Q100-01 (Carlisle)	854-001-02
	-03	NF26Q100-01 (Carlisle) E51426 (PIC)	854-001-03
	-04	F 4704-4 (Draka) E50424 (PIC)	854-001-04
	-05	NF22Q100-01	854-001-05
El Ochito® (1E1, 2E2, 3E3, 3E4, 4E5)	-01	E6A326 (PIC)	858-003-01
	-02	RCN9047-26 (Gore)	858-016-01

* Refer to the RF Datalink & Contacts Catalog for detailed information

280-082P DIMENSIONS




Table 3
Mating Hardware

N Thru-Hole, No Hardware	P Female Jackpost	L Captive Jackscrew, Hex Head, Low Profile
 Dimension: .115/.125 (2.92/3.18)	 Hardware: #4-40 UNC-2A NUT AND LOCKWASHER, #4-40 UNC-2B	 Hardware: RETAINER, #4-40 UNC-2A
K Slot-Head Extended Jackscrew	S Captive Screwlock, Hex Head, Low Profile	T Slot-Head Extended Length, Screwlock
 Dimension: 1.1 (28) MAX Hardware: RETAINER, #4-40 UNC-2A	 Hardware: RETAINER, #4-40 UNC-2A	 Dimension: 1.1 (28) MAX Hardware: RETAINER, #4-40 UNC-2A

Dimensions

Shell Size	A		C Basic		D		E		H	
	In. ±.015	mm. ±.38			In. ±.005	mm. ±.13	In. ±.005	mm. ±.13	In. ±.005	mm. ±.13
1	1.213	30.81	0.984	24.99	0.666	16.92	0.726	18.44	0.745	18.92
2	1.541	39.14	1.312	33.32	0.994	25.25	1.054	26.77	1.075	27.31
3	2.088	53.04	1.852	47.04	1.534	38.96	1.594	40.49	1.615	41.02
4	2.729	69.32	2.500	63.50	2.182	55.42	2.242	56.95	2.260	57.40

NOTES

- Connectors are supplied with unassembled contacts.
- 280-082P pin connectors are intermateable with cable-mount 280-083S socket connectors and with 280-085S and 280-091S printed circuit board connectors.
- When rear panel mounting, order connector without hardware (N option) and order jackpost kit 289-015 separately.
- Connectors are compatible with HiPer-D® protective covers and 289T100 and 289T101 HiPer-D® backshells.