



# IPT Series Tools

## IPT CRIMP TOOLS - PIN CONTACTS

Diagram	Type of contact	Connector Size	A	ØB	ØC	ØD	Conductor Size		MANUAL TOOL	*PNEUMATIC TOOL TYPE "A"	TURRET	INSERTION TOOL		EXTRACTION TOOL					
							mm <sup>2</sup>	AWG											
	10-374-20	20S	8÷18	20,4	1	1,3	1,93	0,2÷0,5	20 22 24	M. 105001	M22520.1.01 AF8 DMC	M. 105003	WA27F DMC	M. 105011 (or M.105008)	M22520/1.02 DMC TH1A (or VH441 DMC)	M. 117346	GLENAIR IT TOOL	M. 118251	GLENAIR IT TOOL
	10-375-20	20	20÷24	24,3	1	1,3	1,93	0,2÷0,5	20 22 24	M. 105001	M22520.1.01 AF8 DMC	M. 105003	WA27F DMC	M. 105011 (or M.105008)	M22520/1.02 DMC TH1A (or VH441 DMC)	M. 117346	GLENAIR IT TOOL	M. 118251	GLENAIR IT TOOL
	10-374-16	16S	8÷18	22,3	1,57	1,72	2,6	0,5÷1	16 18 20	M. 105001	M22520.1.01 AF8 DMC	M. 105003	WA27F DMC	M. 105011 (or M.105008)	M22520/1.02 DMC TH1A (or VH441 DMC)	M. 117083	GLENAIR IT TOOL	M. 118251	GLENAIR IT TOOL
	10-375-16	16	20÷24	24,3	1,57	1,72	2,6	0,2÷0,5	16 18 20	M. 105001	M22520.1.01 AF8 DMC	M. 105003	WA27F DMC	M. 105011 (or M.105008)	M22520/1.02 DMC TH1A (or VH441 DMC)	M. 117083	GLENAIR IT TOOL	M. 118251	GLENAIR IT TOOL
	10-373-12S	12S	8÷18	22,5	2,38	2,5	3,8	2,5÷3	14 12	M. 105001	M22520.1.01 AF8 DMC	M. 105003	WA27F DMC	M. 105012	M22520/1.05	M. 117082	GLENAIR IT TOOL	M. 118250	GLENAIR IT TOOL
	10-373-12	12	8÷18	26,3	2,38	2,5	3,8	2,5÷3	14 12	M. 105001	M22520.1.01 AF8 DMC	M. 105003	WA27F DMC	M. 105012	M22520/1.05	M. 117082	GLENAIR IT TOOL	M. 118250	GLENAIR IT TOOL

## IPT CRIMP TOOLS - SOCKET CONTACTS

Diagram	Type of contact	Connector Size	A	ØB	ØC	ØD	Conductor Size		MANUAL TOOL	*PNEUMATIC TOOL TYPE "A"	TURRET	INSERTION TOOL		EXTRACTION TOOL		GUIDE PIN					
							mm <sup>2</sup>	AWG													
	10-571-20LC	20S	8÷18	20,4	1,08	1,3	1,93	0,2-0,5	20 22 24	M. 105001	M22520.1.01 AF8 DMC	M. 105003	WA27F DMC	M. 105011 (or M.105008)	M22520/1.02 DMC TH1A (or VH441 DMC)	M. 117346	GLENAIR IT TOOL	M. 118251	GLENAIR IT TOOL	M. 125007	GLENAIR IT TOOL
	10-573-20LC	20	20÷24	24,3	1,08	1,3	1,93	0,2-0,5	20 22 24	M. 105001	M22520.1.01 AF8 DMC	M. 105003	WA27F DMC	M. 105011 (or M.105008)	M22520/1.02 DMC TH1A (or VH441 DMC)	M. 117346	GLENAIR IT TOOL	M. 118251	GLENAIR IT TOOL	M. 125007	GLENAIR IT TOOL
	10-571-16LC	16S	8÷18	22,3	1,07	1,72	2,6	0,5 ÷1	16 18 20	M. 105001	M22520.1.01 AF8 DMC	M. 105003	WA27F DMC	M. 105001 (or M.105008)	M22520/1.02 DMC TH1A (or VH441 DMC)	M. 117083	GLENAIR IT TOOL	M. 118251	GLENAIR IT TOOL	M. 125001	GLENAIR IT TOOL
	10-573-16LC	16	20÷24	24,3	1,07	1,72	2,6	0,5-1	16 18 20	M. 105001	M22520.1.01 AF8 DMC	M. 105003	WA27F DMC	M. 105011 (or M.105008)	M22520/1.02 DMC TH1A (or VH441 DMC)	M. 117083	GLENAIR IT TOOL	M. 118251	GLENAIR IT TOOL	M. 125001	GLENAIR IT TOOL
	10-576-12S	12S	8÷18	21,45	2,48	2,5	3,8	2,5÷3	14 12	M. 105001	M22520.1.01 AF8 DMC	M. 105003	WA27F DMC	M. 105012	M22520/1.05	M. 117082	GLENAIR IT TOOL	M. 118250	GLENAIR IT TOOL	M. 125002	GLENAIR IT TOOL
	10-576-12	12	8÷18	25,4	2,48	2,5	3,8	2,5÷3	14 12	M. 105001	M22520.1.01 AF8 DMC	M. 105003	WA27F DMC	M. 105012	M22520/1.05	M. 117082	GLENAIR IT TOOL	M. 118250	GLENAIR IT TOOL	M. 125002	GLENAIR IT TOOL

\* Use together as alternative.