


LOW INSERTION FORCE, HIGH DENSITY LRM Brush Connectors




Insulator assembly BR1-103 Staggered-Grid, Entire Bay, Backplane, Compliant Tail





CONFIGURATION D

HOW TO ORDER			
Sample Part Number	BR1-103	-X	X
Basic Part Number	Staggered-grid, entire bay, backplane, compliant tail		
Configuration	A = 80 Position, Digital H = 108 Digital + 6 Power B = 108 Position, Digital J = 108 Digital + Dual MT C = 152 Position, Digital K = 108 Digital + 270 VDC (#22) D = 180 Position, Digital L = 108 Digital + 270 VDC (#16) E = 108 Digital + 8 Coax M = 108 Digital + Dual 40 Amp (#8) F = 80 Digital + 10 Coax N = 152 Digital + 2 Coax G = 22 Coax		
Termination Stickout	C = Compliant .157 .020 D = Compliant .217 .020 E = Compliant .317 .020		



DIGITAL CONFIGURATIONS





CONFIGURATION A
(80 DIGITAL)




CONFIGURATION B
(108 DIGITAL)



CONFIGURATION C
(152 DIGITAL)



CONFIGURATION D
(180 DIGITAL)




LOW INSERTION FORCE, HIGH DENSITY LRM Brush Connectors





Insulator assembly BR1-103 Staggered-Grid, Entire Bay, Backplane, Compliant Tail



MIXED CONFIGURATIONS (DIGITAL, COAX, POWER, OPTICAL AND HIGH VOLTAGE)





CONFIGURATION E
(108 DIGITAL + 8 COAX)





CONFIGURATION F
(80 DIGITAL + 10 COAX)





CONFIGURATION G
(22 COAX)




CONFIGURATION H
(108 DIGITAL + 6 POWER)



CONFIGURATION J
(108 DIGITAL + DUAL MT)



CONFIGURATION K
(108 DIGITAL + 270 VDC, #22 CONTACTS)




LOW INSERTION FORCE, HIGH DENSITY LRM Brush Connectors




Insulator assembly BR1-103 Staggered-Grid, Entire Bay, Backplane, Compliant Tail


MIXED CONFIGURATIONS (DIGITAL, COAX, HIGH VOLTAGE/CURRENT)



CONFIGURATION **L**
(108 DIGITAL + 270 VDC, #16 CONTACTS)



CONFIGURATION **M**
(108 DIGITAL + 40 AMP, # 8 CONTACTS)



CONFIGURATION **N**
(152 DIGITAL + 2 COAX)