



1770-4052 Code Red Electrical Connector Micro-D Socket Contacts Rear Panel Mount



How To Order Code Red Light Weight Hermetic Micro-D Connectors with Rear Panel Mount						
Sample Part Number	1770-4052	-2	-9	S	S	N
Series	1770-4052 Micro-D Receptacle, Code Red, O-Ring Mount, Socket Contacts					
Shell Material/Plating	1 = Aluminum/cadmium 2 = Aluminum/nickel 3 = Stainless steel/passivated		4 = Aluminum/black anodize 5 = Aluminum/gold 6 = Aluminum/chemfilm			
Contact Layout	9, 15, 21, 25, 31, 37, 51-2, 51, 100					
Contact Type	S = socket					
Termination Type	P = PC tail S = solder pot					
O-Ring Material	Specify per Table II (omit for standard fluorosilicone)					

H

DESIGNATOR	MATERIAL
C	FLUROSILICONE, CONDUCTIVE (CHOSEAL 1298)
E	EPDM (ETHYLENE-PROPYLENE)
V	VITON (FLUOROCARBON; FKM)
N	NITRILE (BUNA-N)
S	SILICONE (ZZ-R-765)
B	BUTYL RUBBER (IIR)
K	KALREZ (FFKM)

Material/finish

Shell: al alloy or stainless steel. See p/n development
 Insulator: thermoplastic; none
 Socket contacts: copper alloy; gold plated
 O-ring: fluorosilicone blend/none
 Interfacial seal: fluorosilicone blend; none
 Sealing compound: polymer encapsulant
 Coil threads: stainless steel/passivated

Notes

1. Marking: "Glenair", part No. and date code in approximate location shown.
2. These hermetic pin connectors mate with all standard MIL-DTL-83513 plug connectors of equivalent size.
3. 9P layout shown for reference only.
4. Connectors supplied with free running coil thd inserts in shell flange.


Performance

- Temperature range: -55°C to +150°C
- DWV (sea level): 150vac; no breakdown
- IR: 5000 MEGOHMS minimum
- Hermeticity: 1 X 10E⁻⁷ cc/sec helium @ 1 atm differential

1770-4052 Code Red Electrical Connector Micro-D Socket Contacts Rear Panel Mount



Micro-D
Hermetic




Dimensions								
NUMBER OF CONTACTS	A MAX	B	C	D MAX	E MAX	F MAX	G MAX	H MAX
9	1.464 (37.19)	0.565 (14.35)	1.000 (25.40)	0.567 (14.40)	1.260 (32.00)	0.445 (11.30)	0.299 (7.59)	0.260 (6.60)
15	1.614 (41.00)	0.715 (18.16)	1.150 (29.21)	0.567 (14.40)	1.410 (35.81)	0.595 (15.11)	0.299 (7.59)	0.260 (6.60)
21	1.764 (44.81)	0.865 (21.97)	1.300 (33.02)	0.567 (14.40)	1.560 (39.62)	0.745 (18.92)	0.299 (7.59)	0.260 (6.60)
25	1.864 (47.35)	0.965 (24.51)	1.400 (35.56)	0.567 (14.40)	1.660 (42.16)	0.845 (21.46)	0.299 (7.59)	0.260 (6.60)
31	2.014 (51.16)	1.115 (28.32)	1.550 (39.37)	0.567 (14.40)	1.810 (45.97)	0.995 (25.27)	0.299 (7.59)	0.260 (6.60)
37	2.164 (54.97)	1.265 (32.13)	1.700 (43.18)	0.567 (14.40)	1.960 (49.78)	1.145 (29.08)	0.299 (7.59)	0.260 (6.60)
51-2	2.514 (63.86)	1.615 (41.02)	2.050 (52.07)	0.567 (14.40)	2.310 (58.67)	1.495 (37.97)	0.299 (7.59)	0.260 (6.60)
51	2.110 (53.59)	1.215 (30.86)	1.650 (41.91)	0.610 (15.49)	1.910 (48.51)	1.055 (26.80)	0.322 (8.18)	0.260 (6.60)
100	2.868 (72.85)	1.800 (45.72)	2.360 (59.94)	0.667 (16.94)	2.670 (67.82)	1.480 (37.59)	0.410 (10.41)	0.310 (7.87)




1770-4052 Code Red Electrical Connector Micro-D Socket Contacts Rear Panel Mount


Contact Layout




9-POSITION




15-POSITION




21-POSITION




25-POSITION



31-POSITION



37-POSITION



51-POSITION (2-ROW)



51-POSITION (3-ROW)



100 POSITION