

GLENAIR SERIES 260 MIL-DTL-26482 Hermetic Series II Type

230-018 Bayonet Coupling Solder Flange Mount Receptacle MS3443 Type



| HOW TO ORDER | | | | | | |
|-------------------------|---|----|---------------------------------------|----|---|---|
| Sample Part Number | 230-018 | FT | 10 | -6 | P | X |
| Series / Basic Part No. | 230-018 = Solder Flange Mount Receptacle | | | | | |
| Material/Finish | Z1 = Stainless Steel/Passivated ZL = Stainless Steel/Nickel Plated FT = C1215 StainlessSteel/Tin Plated (See Note 2) | | | | | |
| Shell Size - Layout | Shell Sizes: 8, 10, 12, 14, 16, 18, 20, 22, 24 Layout per MIL-STD-1669; see Shell Size - Insert Layout table | | | | | |
| Contact Type | P = Pin, Solder Cup S = Socket, Solder Cup | | X = Pin, Eyelet Z = Socket, Eyelet | | | |
| Alt. Polarization | W, X, Y, Z, Omit for normal | | | | | |

| HERMETIC LEAK RATE MOD CODES | |
|------------------------------|--|
| Designator | Required Leak Rate |
| -585A | 1 x 10 ⁻¹⁰ cc Helium per second |
| -585B | 1 x 10 ⁻⁹ cc Helium per second |
| -585C | 1 x 10 ⁻⁸ cc Helium per second |

| SHELL SIZE - INSERT LAYOUT | | | | | | | | | | | | | | | |
|----------------------------|-----------------|----|----|---------------------|-----------------|----|----|---------------------|-----------------|----|----|---------------------|-----------------|----|----|
| Shell Size - Layout | Size / Quantity | | | Shell Size - Layout | Size / Quantity | | | Shell Size - Layout | Size / Quantity | | | Shell Size - Layout | Size / Quantity | | |
| | 20 | 16 | 12 | | 20 | 16 | 12 | | 20 | 16 | 12 | | 20 | 16 | 12 |
| 8-2 | 2 | | | 14-9 | 5 | | 4 | 18-11 | | 11 | | 22-19 | | | 19 |
| 8-3 | 3 | | | 14-12 | 8 | 4 | | 18-30 | 29 | 1 | | 22-21 | | 21 | |
| 8-4 | 4 | | | 14-15 | 14 | 1 | | 18-32 | 32 | | | 22-32 | 32 | | |
| 8-33 | 3 | | | 14-18 | 18 | | | 18-85 | 5 | | 8 | 22-34 | 34 | | |
| 8-98 | 3 | | | 14-19 | 19 | | | 20-16 | | 16 | | 22-41 | 27 | 14 | |
| 10-6 | 6 | | | 14-22 | 1 | | 4 | 20-24 | 24 | | | 22-55 | 55 | | |
| 10-98 | 6 | | | 16-8 | | 8 | | 20-27 | 27 | | | 22-95 | 26 | | 6 |
| 12-3 | | 3 | | 16-14 | 8 | | 6 | 20-39 | 37 | 2 | | 24-19 | | | 19 |
| 12-8 | 8 | | | 16-23 | 22 | 1 | | 20-41 | 41 | | | 24-27 | 11 | | 16 |
| 12-10 | 10 | | | 16-26 | 26 | | | 20-90 | 3 | | 12 | 24-31 | | 31 | |
| 14-4 | | | 4 | 16-99 | 21 | 2 | | 22-12 | | | 12 | 24-61 | 61 | | |
| 14-5 | | 5 | | 18-8 | | | 8 | 22-19 | | | | | | | 19 |

NOTES

- To be identified with manufacturer's name, part number and date code, space permitting.
- Material/Finish:
 - Shell: per part number development Titanium and Inconel[®] available. Consult factory.
 - Contacts: 52 Nickel alloy/gold plate.
 - Sockets: copper alloy, gold plated.
 - Bayonets: stainless steel/passivate.
 - Seals: silicone elastomer
 - Insulation: glass
 - Socket: rigid dielectric
- Performance
 - Hermeticity: <1 x 10⁻⁷ cc/sec @ 1 atm differential.
 - Dielectric withstanding voltage: Consult factory or MIL-STD-1669.
 - Insulation resistance: 5000 megohms min @500VDC.
- Consult factory and/or MIL-STD-1669 for arrangement and insert position options.
- Glenair 230-018 will mate with any QPL MIL-DTL-26482 Series II bayonet coupling plug of same size and insert polarization.

GLENAIR SERIES 260 MIL-DTL-26482 Hermetic Series II Type



230-018 Bayonet Coupling Solder Flange Mount Receptacle MS3443 Type




TABLE I: CONNECTOR AND CUT-OUT DIMENSIONS

| Shell Size | A Dia ± .010 (0.3) | C Dia Mounting Locator | D Dia Min | F | J | K | L | P | V | Max Weight (Lbs.) |
|------------|-----------------------|------------------------------|--------------|--------------------------|------------------------|--------------|-------------|------------------------|------------------------|-------------------------|
| 8 | .625 (15.9) | .563/.557 (14.3/14.1) | .403 (10.2) | .598/.578 (15.2/14.7) | .156/.116 (4.0/2.9) | .570 (14.5) | .801 (20.3) | .178/.118 (4.5/3.0) | .248/.188 (6.3/4.8) | .0310 |
| 10 | .750 (19.1) | .673/.667 (17.1/16.9) | .515 (13.1) | .598/.578 (15.2/14.7) | .156/.116 (4.0/2.9) | .680 (17.3) | .801 (20.3) | .178/.118 (4.5/3.0) | .248/.188 (6.3/4.8) | .0340 |
| 12 | .844 (21.4) | .782/.776 (19.9/19.7) | .630 (16.0) | .598/.578 (15.2/14.7) | .156/.116 (4.0/2.9) | .789 (20.0) | .801 (20.3) | .178/.118 (4.5/3.0) | .248/.188 (6.3/4.8) | .0400 |
| 14 | .969 (24.6) | .907/.901 (23.0/22.9) | .755 (19.2) | .598/.578 (15.2/14.7) | .156/.116 (4.0/2.9) | .914 (23.2) | .801 (20.3) | .178/.118 (4.5/3.0) | .248/.188 (6.3/4.8) | .0510 |
| 16 | 1.094 (27.8) | 1.032/1.026 (26.2/26.1) | .880 (22.4) | .598/.578 (15.2/14.7) | .156/.116 (4.0/2.9) | 1.039 (26.4) | .801 (20.3) | .178/.118 (4.5/3.0) | .248/.188 (6.3/4.8) | .0620 |
| 18 | 1.218 (30.9) | 1.157/1.151 (29.4/29.2) | .980 (24.9) | .598/.578 (15.2/14.7) | .156/.116 (4.0/2.9) | 1.164 (29.6) | .801 (20.3) | .178/.118 (4.5/3.0) | .248/.188 (6.3/4.8) | .0820 |
| 20 | 1.312 (33.3) | 1.251/1.245 (31.8/31.6) | 1.105 (28.1) | .660/.640 (16.8/16.3) | .156/.116 (4.0/2.9) | 1.258 (32.0) | .863 (21.9) | .178/.118 (4.5/3.0) | .248/.188 (6.3/4.8) | .1000 |
| 22 | 1.438 (36.5) | 1.376/1.371 (35.0/34.8) | 1.230 (31.2) | .660/.640 (16.8/16.3) | .188/.148 (4.8/3.8) | 1.383 (35.1) | .895 (22.7) | .146/.086 (3.7/2.2) | .216/.156 (5.5/4.0) | .1150 |
| 24 | 1.564 (39.7) | 1.501/1.495 (38.1/38.0) | 1.385 (35.2) | .660/.640 (16.8/16.3) | .188/.148 (4.8/3.8) | 1.508 (38.3) | .895 (22.7) | .146/.086 (3.7/2.2) | .216/.156 (5.5/4.0) | .2680 |