

SERIES 805 TRIPLE-START ACME THREAD Mighty Mouse Connectors and Cables



Glass-Sealed Hermetic Receptacle with Solder Cups and Integral Shield Termination Platform



PCB Hermetic Receptacle Connectors feature integral banding porch for use with Band-Master® stainless steel band (sold separately) and power and signal solder cup contacts for direct to wire attachment. Available square flange-front or rear panel mount, solder mount, jam-nut, and weld mount shell styles. Connectors are 100% tested to meet 1×10^{-7} ccHe/sec at 1 atm helium leak rate. Contacts are non-removable, back potted, and parylene compatible. Consult factory for additional arrangements.

How To Order						
Sample Part Number		805-019	-02	Z1	8-7	P A
Series	805-019 = Hermetic Receptacle with Solder Cups and Integral Banding Porch					
Shell Style (See Table I)	-02 = Square Flange, Front or Rear Mount Receptacle -03 = Solder Mount Receptacle -07 = Jam-Nut, Rear Panel Mount Receptacle					
Material and Finish	Z1 = Stainless Steel / Passivated ZB = Stainless Steel / Olive Drab Chromate over Cadmium ZC = Stainless Steel / Zinc Cobalt Alloy/Black Chromate ZL = Stainless Steel / Electrodeposited Nickel ZN = Stainless Steel / Zinc Nickel/Olive Drab over Electroless Nickel ZU = Stainless Steel / Cadmium Black					
Shell Size - Insert Arrangement	See page J-6. See section B for PCB footprints					
Contact Type	P = Pin, Solder Cup S = Socket, Solder Cup					
Shell Key Positions (See Table II)	A = Normal B = Pos. B C = Pos. C D = Pos. D E = Pos. F F = Pos. F					


Table I: Shell Style		
-02 Square Flange	-07 Jam-Nut	-03 Solder Mount

Table II: Key Positions		
Position	A	B
A (Normal)	150°	210°
B	75°	210°
C	95°	230°
D	140°	275°
E	75°	275°
F	95°	210°

DWV Rating	
Contact Sizes	Test Voltage
23	750 Vac
20 HD	1000 Vac
16, 12, 8	1800 Vac

NOTES

1. This connector mates with all quick coupling high density plug connectors with same polarization and opposite contact gender 805-001, 805-002
2. For additional insert arrangements consult factory
3. Contacts are non removable and connector is back potted
4. Hermeticity is less than 1×10^{-7} ccHe/second at one atmosphere
5. See page J-11 for recommended panel cut-out




SERIES 805 TRIPLE-START ACME THREAD Mighty Mouse Connectors and Cables




Glass-Sealed Hermetic Receptacle with Solder Cups and Integral Shield Termination Platform


SQUARE FLANGE RECEPTACLE - SHELL STYLE 02




SOLDER MOUNT RECEPTACLE - SHELL STYLE 03



JAM-NUT MOUNT RECEPTACLE - SHELL STYLE 07





SERIES 805 TRIPLE-START ACME THREAD Mighty Mouse Connectors and Cables




Glass-Sealed Hermetic Receptacle with Solder Cups and Integral Shield Termination Platform

Table III: 805-019 Dimensions


Shell Size	A Sq	B Bsc	Ø C	Ø D	E Flat	F Flat	J Holes	K Thread	Ø P	Ø W
8	.850 (21.59)	.660 (16.76)	1.150 (29.21)	.760 (19.30)	.730 (18.54)	.535 (13.59)	.096 (2.44) .091 (2.31)	.5000-.1P-.3L-TS	.625 (15.88)	.316 (8.03)
9	.913 (23.19)	.723 (18.36)	1.230 (31.24)	.880 (22.35)	.850 (21.59)	.661 (16.79)		.5625-.1P-.3L-TS	.688 (17.48)	.397 (10.08)
10	.975 (24.76)	.785 (19.94)	1.330 (33.78)	.880 (22.35)	.850 (21.59)	.661 (16.79)		.6250-.1P-.3L-TS	.750 (19.05)	.472 (11.99)
11	1.039 (26.39)	.848 (21.54)	1.410 (35.81)	.955 (24.26)	.925 (23.50)	.721 (18.31)		.6875-.1P-.3L-TS	.812 (20.62)	.519 (13.18)
12	1.099 (27.91)	.909 (23.09)	1.500 (38.10)	1.060 (26.92)	1.035 (26.29)	.784 (19.91)		.7500-.1P-.3L-TS	.875 (22.23)	.585 (14.86)
15	1.288 (32.72)	1.058 (26.87)	1.750 (44.45)	1.203 (30.56)	1.173 (29.79)	.970 (24.64)	.130 (3.30) .126 (3.20)	.9375-.1P-.3L-TS	1.062 (26.97)	.687 (17.45)
18	1.475 (37.47)	1.255 (31.88)	2.000 (50.80)	1.389 (35.28)	1.359 (34.52)	1.147 (29.13)		1.1250-.1P-.3L-TS	1.250 (31.75)	.884 (22.45)
19	1.537 (39.04)	1.327 (33.71)	2.094 (53.19)	1.450 (36.83)	1.420 (36.07)	1.221 (31.01)		1.1875-.1P-.3L-TS	1.312 (33.32)	.884 (22.45)
21	1.663 (42.24)	1.452 (36.88)	2.270 (57.66)	1.58 (40.13)	1.550 (39.37)	1.35 (34.29)		1.3125-.1P-.3L-TS	1.438 (36.53)	1.003 (25.48)
23	1.787 (45.39)	1.576 (40.03)	2.440 (61.98)	1.705 (43.31)	1.675 (42.55)	1.470 (37.34)		1.4375-.1P-.3L-TS	1.562 (39.67)	1.134 (28.80)

Panel Cut-Out Dimensions

Shell Size	Jam-Nut, Rear Panel Mount		Square Flange, Rear Panel Mount		
	G Flat	Ø H	H BSC	J Holes	Ø P
8	.545 (13.84) .541 (13.74)	.572 (14.53) .567 (14.40)	.660 (16.76)	.096 (2.43) .091 (2.31)	.515 (13.08)
9	.671 (17.04) .667 (16.94)	.698 (17.73) .693 (17.60)	.723 (18.36)		.578 (14.68)
10	.671 (17.04) .667 (16.94)	.698 (17.73) .693 (17.60)	.785 (19.94)		.640 (16.26)
11	.731 (18.57) .727 (18.47)	.760 (19.30) .755 (19.18)	.848 (21.54)		.703 (17.86)
12	.794 (20.17) .790 (20.07)	.822 (20.88) .817 (20.75)	.909 (23.09)		.765 (19.43)
13	.851 (21.62) .847 (21.51)	.885 (22.48) .881 (22.38)	.973 (24.71)	.130 (.13) .126 (3.20)	.828 (21.03)
15	.980 (24.89) .976 (24.79)	1.010 (25.65) 1.005 (25.53)	1.058 (26.87)		.953 (24.21)
18	1.157 (29.39) 1.153 (29.29)	1.198 (30.43) 1.193 (30.30)	1.255 (31.88)		1.140 (28.96)
19	1.231 (31.27) 1.227 (31.17)	1.260 (32.00) 1.255 (31.88)	1.327 (33.71)		1.203 (30.56)
21	1.358 (34.49) 1.354 (34.39)	1.383 (35.13) 1.381 (35.08)	1.452 (36.88)		1.328 (33.73)
23	1.480 (37.59) 1.476 (37.49)	1.510 (38.35) 1.505 (38.23)	1.570 (39.88)		1.453 (36.91)



Recommended Panel Cutout
-07 Jam-Nut, Rear Panel Mount



Recommended Panel Cutout
-02 Square Flange, Rear Panel Mount Only

Material/Finish:

- Shell: SST / passivate or plate as required
- Contacts, hermetic: alloy 52 / gold plate
- Contacts, socket: copper alloy / gold plate
- Seals: fluorosilicone / N.A.
- Insulator, hermetic: fused vitreous glass / N.A.
- Insulator, socket: rigid dielectric / N.A.