


SERIES 89 NANOMINIATURE Single and Dual Row Nano Strip Connectors



891-047 Dual Row, Plastic Shell, Nano Strip Connector with Uninsulated Wire

SINGLE AND DUAL ROW NANO STRIP CONNECTORS




Nano Strip Connectors with Uninsulated Wire feature gold alloy TwistPin contacts. Contacts are precision-crimped to Insulated wire. These nanominiature strip connectors offer premium performance and reliability for demanding applications. Wire gages #30 and #32 AWG.

TwistPin Contact System assures premium performance in demanding environments. The gold alloy contacts will stand up to years of exposure without corrosion.

Typical Applications include UAVs, satellites, missile systems and geophysical instruments.

HOW TO ORDER	
Sample Part Number	891-047 -22 P -0 B .125 -P1 MH
Series	891-047 = Dual row plastic shell Nano Strip connector with uninsulated wire
Number of Cavities	2 thru 80 = Total number of cavities including cavities used for guide pins and disabled cavities used for mounting holes, if any. See Table I
Contact Type	P = Pin (plug) S = Socket (receptacle)
Wire Gage	0 = #30 AWG 2 = #32 AWG
Wire Type	D3 = Single strand copper wire, uninsulated with gold plating
Wire Length	.125, .250, .375, .500; length in inches
Optional Guide Pin	Omit for no guide pin (Guide pin in receptacle, accepts guide pin in plug) P1 = Guide pin or accepts guide pin in position 1 (add 1 cavity to number of active contacts) PB = Guide pin or accepts guide pin in 1 and last position (add 2 cavities to number of active contacts) PX = Guide pin or accepts guide pin in position specified by "X" (add 1 cavity to number of active contacts)
Optional Mounting Holes	Omit for no mounting holes MH = Mounting holes (add 12 cavities to number of active contacts)

NUMBER OF CAVITIES EXAMPLE
8 ACTIVE CONTACTS
+2 PB GUIDE PINS
+12 MOUNTING HOLES
22 TOTAL



PERFORMANCE SPECIFICATIONS	
Contact Spacing: .025" (0.64) contact centers	Contact Resistance: 71 millivolt drop maximum, 1 AMP current, any catalog supported wire type
Wire Accommodation: #30-#32 AWG	Corrosion Resistance: 48 hour salt spray IAW EIA-364-26, Condition B
Current Rating: 1 AMP maximum tested per EIA-364-70	Humidity: 240 hours, IAW EIA-364-31, Test Condition B
DWV: 250 VAC RMS sea level, 100 VAC RMS 70,000 feet per EIA-364 Procedure 20	Contact Engaging/Separation Force: 5 ounce maximum, 0.4 ounce minimum
Insulation Resistance: 5000 Megohms minimum test voltage 100 VDC, per EIA-364 Procedure 21	Thermal Vacuum Outgassing: Total mass loss (TML) 1.0% max., volatile condensable material (VCM) 0.1% max. IAW ASTM E595
Operating Temperature: -55° C. to +125° C.	

SERIES 89 NANOMINIATURE Single and Dual Row Nano Strip Connectors



891-047 Dual Row, Plastic Shell, Nano Strip Connector with Uninsulated Wire




TABLE I : DIMENSIONS

Number Cavities	A	C See Note 4
2	0.050 (1.27)	N/A
4	0.075 (1.91)	N/A
6	0.100 (2.54)	N/A
8	0.125 (3.18)	N/A
10	0.150 (3.81)	N/A
12	0.175 (4.45)	N/A
14	0.200 (5.08)	0.100 (2.54)
16	0.225 (5.72)	0.125 (3.18)
18	0.250 (6.35)	0.150 (3.81)
20	0.275 (6.99)	0.175 (4.45)
22	0.300 (7.62)	0.200 (5.08)
24	0.325 (8.26)	0.225 (5.72)
26	0.350 (8.89)	0.250 (6.35)
28	0.375 (9.53)	0.275 (6.99)
30	0.400 (10.16)	0.300 (7.62)
32	0.425 (10.80)	0.325 (8.26)
34	0.450 (11.43)	0.350 (8.89)
36	0.475 (12.07)	0.375 (9.53)
38	0.500 (12.70)	0.400 (10.16)
40	0.525 (13.34)	0.425 (10.80)
42	0.550 (13.97)	0.450 (11.43)
44	0.575 (14.61)	0.475 (12.07)
46	0.600 (15.24)	0.500 (12.70)
48	0.625 (15.88)	0.525 (13.34)
50	0.650 (16.51)	0.550 (13.97)
52	0.675 (17.15)	0.575 (14.61)
54	0.700 (17.78)	0.600 (15.24)
56	0.725 (18.42)	0.625 (15.88)
58	0.750 (19.05)	0.650 (16.51)
60	0.775 (19.69)	0.675 (17.15)
62	0.800 (20.32)	0.700 (17.78)
64	0.825 (20.96)	0.725 (18.42)
66	0.850 (21.59)	0.750 (19.05)
68	0.875 (22.23)	0.775 (19.69)
70	0.900 (22.86)	0.800 (20.32)
72	0.925 (23.50)	0.825 (20.96)
74	0.950 (24.13)	0.850 (21.59)
76	0.975 (24.77)	0.875 (22.23)
78	1.000 (25.40)	0.900 (22.86)
80	1.025 (26.04)	0.925 (23.50)

SINGLE AND DUAL ROW NANO STRIP CONNECTORS

NOTES

1. Material and Finishes:
 - Shell: polyphenylene sulfide (PPS)
 - Contacts: gold alloy / unplated
 - Wire: see part number break down
 - Optional guide pin: stainless steel, passivated
2. Inspect and test IAW MIL-DTL-32139 where applicable
3. Strip shell may have a half cavity on either end or each end
4. Only applies if ordered with optional mounting holes