


# SERIES 89 NANOMINIATURE Threaded and Breakaway Nano Circulars



## 899-020 Nano Circular Replacement Panel O-Ring

THREADED AND BREAKAWAY NANO CIRCULARS



**Replacement Panel O-Ring** for front or rear panel mount Nano Circular connectors. IAW MIL-DTL-25988 Type II, Class I, Grade 70 fluorosilicone.

HOW TO ORDER				
<b>Sample Part Number</b>	<b>899-020</b>	<b>-1</b>	<b>F</b>	<b>-01</b>
<b>Series</b>	899-020 = Nano Circular Replacement Panel O-ring			
<b>Shell Size</b>	1, 2, 3, 4			
<b>Mounting</b>	F = Front Panel Mount R = Rear Panel Mount			
<b>Material/Finish</b>	01 = Fluorosilicone IAW MIL-DTL-25988 Type II, Class I, Grade 70			

DIMENSIONS		
FPM SHELL SIZE	RPM SHELL SIZE	ID
N/A	1	.3125 (7.94) ±.0045 (0.11)
1	2	.3725 (9.46) ±.0055 (0.14)
2	3	.4130 (10.49) ±.0060 (0.15)
3	4	.4525 (11.49) ±.0065 (0.17)
4	N/A	.5120 (13.00) ±.0070 (0.18)

