



Performance Specification					
TEST DESCRIPTION	REQUIREMENT			PROCEDURE	
Contact resistance, glass-sealed hermetic connectors	Contact Size, Wire Size	Test Current Amperes	Maximum Millivolt Drop		MIL-DTL-38999M Para. 3.18.2 EIA-364-06
			Initial	After Conditioning	
	20	5	60	75	
	22	3	85	95	
Shell-to-shell conductivity	Finish Code	Shell Matl/Fin	Millivolt Drop (mV)		MIL-DTL-38999M Para. 4.5.25 EIA-364-83
	NF	Al/OD Cad	2.5		
	MT	Al/Ni-PTFE	2.5		
	ME	Al/EN	1.0		
	ZR	Al/Zn-Ni	2.5		
	Z1	SST/pass.	10.0		
Backshell shield braid to shell conductivity	Finish Code	Shell Matl/Fin	Millivolt Drop (mV)		MIL-DTL-38999M Para. 4.5.25.1 EIA-364-83
	NF	Al/OD Cad	5.0		
	MT	Al/Ni-PTFE	5.0		
	ME	Al/EN	3.5		
	ZR	Al/Zn-Ni	5.0		
	Z1	SST/pass.	15.0		
Indirect lightning strike	No evidence of damage which could impair proper functioning. Connectors shall meet shell-to-shell conductivity, DWV and coupling torque.			MIL-DTL-38999M Para. 4.5.47 EIA-364-75 10,000 Amps peak current	
	EMI shielding	Leakage Attenuation, (dB) minimum		MIL-DTL-38999M Para. 4.5.28	
	Freq. MHz	Electroless Nickel Finish	Cadmium, Nickel-PTFE, Zinc-Nickel Finish		
	100	90	90		
	200	88	88		
	300	88	88		
	400	87	87		
	800	85	85		
	1,000	85	85		
	1,500	76	69		
	2,000	70	65		
	3,000	69	61		
	4,000	68	58		
	6,000	66	55		
	10,000	65	50		
Durability	No evidence of damage which could impair proper functioning following 500 cycles of mating and unmating.			MIL-DTL-38999M Para. 4.5.8 EIA-364-09	
Coupling and uncoupling torque	Shell size	Maximum Engagement lbs.-inch.	Minimum Disengagement lbs.-inch.		MIL-DTL-38999M Para. 4.5.7 EIA-364-114
	8	8	2		
	9	8	2		
	10	12	2		
	11	12	2		
	12	12	2		
	14	16	2		
	16	20	3		
	18	24	3		
	20	28	3		
	22	32	5		
	24	36	5		
	Insert retention	100 pounds per square inch, 25 pound minimum force			
External bend moment	Shell size	Pound inches			MIL-DTL-38999M Para. 4.5.16 EIA-364-43
	8	100			
	9	100			
	10	100			
	11	200			
	12	300			
	14	400			
	16	500			
	18	600			
	20	700			
	22	800			
	24	900			



Performance Specification																							
TEST DESCRIPTION	REQUIREMENT	PROCEDURE																					
Contact retention	<table border="1"> <thead> <tr> <th>Contact size</th> <th>Pounds ± 10 percent</th> </tr> </thead> <tbody> <tr> <td>22HD</td> <td>10</td> </tr> <tr> <td>20HD</td> <td>10</td> </tr> </tbody> </table>	Contact size	Pounds ± 10 percent	22HD	10	20HD	10	MIL-DTL-38999M Para. 4.5.20.1 EIA-364-29															
Contact size	Pounds ± 10 percent																						
22HD	10																						
20HD	10																						
Magnetic permeability	2 μ maximum	MIL-DTL-38999M Para. 4.5.48 EIA-364-54																					
Contact engaging /separation force	Contact forces shall meet AS39029 Table 9 requirements	AS39029C Para. 4.7.6 EIA-364-37																					
Temperature cycling (thermal shock)	No evidence of damage detrimental to the function of the connector	MIL-DTL-38999M Para. 4.5.4 EIA-364-32 Mated connectors, -65° C to +200° C																					
Random vibration, elevated temperature, 43g rms	No discontinuities of 1 microsecond or longer No resonance at frequencies less than 300 Hz	MIL-DTL-38999M Para. 4.5.23.2.3 with Figure 24 accessory load EIA-364-28 +200° C																					
Random vibration, ambient temperature, 49g rms	No discontinuities of 1 microsecond or longer	MIL-DTL-38999M Para. 4.5.23.2.4 EIA-364-28 Test Condition V																					
Sine vibration, 60g	No discontinuities of 1 microsecond or longer	MIL-DTL-38999M Para. 4.5.23.2.1 with Figure 24 accessory load 12 hours in each of 3 axes 4 hours at ambient, 4 hours at -55° C, 4 hours at +200° C																					
Mechanical shock, 300g	No discontinuities of 1 microsecond or longer	MIL-DTL-38999M Para. 4.5.24.1 EIA-364-27																					
High impact shock (901)	No discontinuities of 1 microsecond or longer No evidence of damage which could impair proper functioning.	MIL-DTL-38999M Para. 4.5.24.2 MIL-S-901 Grade A																					
Humidity, cyclic	Meet DWV and IR test	MIL-DTL-38999M Para. 4.5.26 EIA-364-31 Method 4 10 cycles, 10 days, 25 – 65° C 80 – 100% RH																					
Ozone exposure	No evidence of damage detrimental to the function of the connector	MIL-DTL-38999M Para. 4.5.29 EIA-364-14																					
Fluid immersion	No damage to plastic, elastomeric and bonding materials detrimental to the function of the connector. Connector shall meet coupling torque and DWV requirements when tested within 3 hours of immersion.	MIL-DTL-38999M Para. 4.5.30 EIA-364-10																					
Altitude immersion	No evidence of moisture on connector interface or contacts. At the end of the third cycle, while still submersed, connectors shall meet dielectric withstanding voltage and 1,000 megohms insulation resistance.	MIL-DTL-38999M Para. 4.5.9 EIA-364-03 75,000 feet																					
Altitude- low temperature	Connectors shall meet insulation resistance requirement while at -65° C and 100,000 ft. Connectors shall meet DWV requirement when returned to ambient conditions.	MIL-DTL-38999M Para. 4.5.21 EIA-364-105 -65° C 100,000 ft.																					
Thermal vacuum outgassing	All nonmetallic materials shall not exceed 1.0% Total Mass Loss and 0.1% Total Volatile Condensable Materials. Applicable only to connectors that have been subjected to optional thermal vacuum outgassing.	MIL-DTL-38999M Para. 4.5.42 ASTM E595																					
Salt Spray (dynamic)	<table border="1"> <thead> <tr> <th>Finish Code</th> <th>Matl/Fin</th> <th>Hours</th> </tr> </thead> <tbody> <tr> <td>NF</td> <td>Al/OD Cad</td> <td>500</td> </tr> <tr> <td>MT</td> <td>Al/Ni-PTFE</td> <td>500</td> </tr> <tr> <td>ME</td> <td>Al/EN</td> <td>96</td> </tr> <tr> <td>ZR</td> <td>Al/Zn-Ni</td> <td>500</td> </tr> <tr> <td>Z1</td> <td>SST/passivate</td> <td>1000</td> </tr> <tr> <td>ZL</td> <td>SST/Ni</td> <td>1000</td> </tr> </tbody> </table>	Finish Code	Matl/Fin	Hours	NF	Al/OD Cad	500	MT	Al/Ni-PTFE	500	ME	Al/EN	96	ZR	Al/Zn-Ni	500	Z1	SST/passivate	1000	ZL	SST/Ni	1000	MIL-DTL-38999M Para. 4.5.13.2 EIA-364-26 500 mating cycles
Finish Code	Matl/Fin	Hours																					
NF	Al/OD Cad	500																					
MT	Al/Ni-PTFE	500																					
ME	Al/EN	96																					
ZR	Al/Zn-Ni	500																					
Z1	SST/passivate	1000																					
ZL	SST/Ni	1000																					