


MISSION-CRITICAL
INTERCONNECT
SOLUTIONS



Glenair
SIGNATURE SERIES



Super ITS - IFO High Data-Rate Fiber Optic Connectors

Singlemode and Multimode Fiber Optic Connectors for
Harsh Industrial and Rail Applications



RUGGED REVERSE-BAYONET

Super ITS - IFO B Fiber Optic Connectors

High-speed, high data rate fiber optic connectors for harsh environmental conditions

Glenair Super ITS - IFO B connectors meet the need for high-speed, multi-gigabit data transmission in rugged harsh environments such as armored combat support vehicles, communications shelters and bunkers, military aircraft, harsh wayside rail applications, and more. These optical fiber-equipped interconnects far outstrip the data carrying capacity and speed of conventional copper wire systems. Super ITS - IFO B interconnects pack orders of magnitude more data with almost instantaneous delivery to the user, and are immune to all forms of electromagnetic interference.

Glenair Super ITS - IFO B fiber optic connectors are available with 2, 4, 6 or 12 termini configurations. Termini accommodate 9/125 (Singlemode), 50/125 and 62/125 (Multimode) optical fibers with a maximum 1.4dB insertion loss. Backshells and adapters are engineered to minimize bend radius and provide strain relief with design improvements such as integral wire sealing grommets and retractable conduit fittings. Fiber optic cleaning and inspection toolkits as well as fiber optic termination training and certification are also available.



Features:

- EMI and spark/arc immunity for high-reliability settings
- 2, 4, 6, or 12 fiber optic termini configurations available
- Termini accommodate 9/125 (Singlemode), 50/125 and 62/125 (Multimode) optical fibers
- Turnkey high-speed fiber optic interconnect cables and harnesses available
- Environmentally sealed (IP67)
- UL94-V0 compliant fiber optic cable
- Integrated optical media alignment grommet

RUGGED REVERSE-BAYONET

Super ITS-IFO B High-Speed High-Data Rate Fiber Optic Connectors



Product Selection Guide



Super ITS - IFO B Fiber Optic Connectors

**2-Pole fiber optic, shell size 10SL connector with environmental sealing
PHM or Strain Relief PHM backshell**



Super ITS - IFO B Fiber Optic Connectors

**4-Pole fiber optic, shell size 16S connector with environmental sealing
strain relief backshell and Kevlar fiber retention**



Super ITS - IFO B Fiber Optic Connectors

**6-Pole fiber optic, shell size 24 connector with environmental sealing PG
backshell for conduit termination or PGSW backshell with strain relief for use
with jacketed cables**



Super ITS - IFO B Fiber Optic Connectors

**12-Pole fiber optic, shell size 32 fiber optic connector with environmental
sealing PG backshell for conduit termination**



MISSION-CRITICAL INTERCONNECT SOLUTIONS

Glenair, Inc.

1211 Air Way • Glendale, California • 91201-2497

Telephone: 818-247-6000 • Fax: 818-500-9912 • sales@glenair.com

www.glenair.com

Glenair East

20 Sterling Drive
Wallingford, CT
06492

Telephone:
203-741-1115
Facsimile:
203-741-0053
sales@glenair.com

Glenair UK Ltd

40 Lower Oakham Way
Oakham Business Park
Mansfield, Notts
NG18 5BY England

Telephone:
+44-1623-638100
Facsimile:
+44-1623-638111
sales@glenair.co.uk

Glenair Microway Systems

7000 North Lawndale Avenue
Lincolnwood, IL
60712

Telephone:
847-679-8833
Facsimile:
847-679-8849

Glenair Nordic AB

Gustav III : S Boulevard 42
SE-169 27 Solna
Sweden

Telephone:
+46-8-50550000
sales@glenair.se

Glenair GmbH

Schaberweg 28
61348 Bad Homburg
Germany

Telephone:
06172 / 68 16 0
Facsimile:
06172 / 68 16 90
info@glenair.de

Glenair Iberica

C/ La Vega, 16
45612 Velada
Spain

Telephone:
+34-925-89-29-88
Facsimile:
+34-925-89-29-87
sales@glenair.es

Glenair Italia S.p.A.

Via Del Lavoro, 7
40057 Quarto Inferiore –
Granarolo dell'Emilia
Bologna, Italy

Telephone:
+39-051-782811
Facsimile:
+39-051-782259
info@glenair.it

Glenair France SARL

7, Avenue Parmentier
Immeuble Central Parc #2
31200 Toulouse
France

Telephone:
+33-5-34-40-97-40
Facsimile:
+33-5-61-47-86-10
sales@glenair.fr

Glenair Korea

6-21Tapsil-ro 58beon-gil
Giheung-gu, Yongin-si
Gyeonggi-do
Republic of Korea

Telephone:
+82-31-8068-1090
Facsimile:
+82-31-8068-1092
sales@glenair.kr