


# Semper Tan EMI/RFI Helical Tubing Assembly



Sym	Tubing Material
E	ETFE, Tefzel
F	FEP, Fluoropolymer
K	PEEK
P	PFA, Fluoropolymer

Sym	Braided Shield
B	Bronze
C	Stainless Steel
N	Nickel Copper
S	SnCuFe
T	Tin Copper

Dash No	Fractional Size Ref	A Inside Dia		B Dia Max
		Min	Max	
06	3/16	0.181 (4.6)	0.188 (4.8)	0.490 (0.5)
09	9/32	0.273 (6.9)	0.281 (7.1)	0.584 (0.6)
10	5/16	0.306 (7.8)	0.312 (7.9)	0.620 (0.6)
12	3/8	0.359 (9.1)	0.375 (9.5)	0.680 (0.7)
14	7/16	0.427 (10.8)	0.437 (11.1)	0.741 (0.7)
16	1/2	0.480 (12.2)	0.500 (12.7)	0.820 (0.8)
20	5/8	0.603 (15.3)	0.625 (15.9)	0.940 (0.9)
24	3/4	0.725 (18.4)	0.750 (19.1)	1.000 (1.0)
28	7/8	0.860 (21.8)	0.875 (22.2)	1.243 (1.2)
32	1	0.970 (24.6)	1.000 (25.4)	1.396 (1.4)
40	1 1/4	1.205 (30.6)	1.250 (31.8)	1.709 (1.7)
48	1 1/2	1.437 (36.5)	1.500 (38.1)	2.002 (2.0)
56	1 3/4	1.688 (42.9)	1.750 (44.5)	2.252 (2.3)
64	2	1.937 (49.2)	2.000 (50.8)	2.502 (2.5)