


SuperNine Series I Bayonet PowerPlay
660-140 Plug Cover

SUPERNINE SERIES I POWERPLAY BAYONET





MATERIAL/FINISH

- Hardware, rivet: CRES/passivate
- Sealant, rivet: two part epoxy
- Rope attachments: Per Attachment Rings Style Table
- Gasket - silicone

NOTES

- Max diameter over which mandrel will rotate freely shown in Attachment Ring Table.
- Length tolerance for sash chain (s) is ± one (1) link, for all other attachments ± .25.

ATTACHMENT TYPE




Symbol	Attachment
F	Wire Rope, Nylon Jacket with Terminal
G	.094 Dia Nylon Cord (Black) with Loop Ends
H	Wire Rope, Teflon Jacket with Terminal
N	Attachment Omitted
R	Wire Rope, PVC Jacket with Terminal
T	Wire Rope, No Jacket, with Terminal
K	Nylon Rope
S	#8 Sash Chain, CRES, Passivate

HOW TO ORDER

Sample Part Number	660-140	ME	13	R	6	-01
Basic Part Number	660-140 PowerPlay Plug Cover					
Material/Finish	ME = Aluminum Alloy, Electroless Nickel MT = Aluminum Alloy, Nickel-PTFE NF = Aluminum Alloy, Cad/O. D. Over Electroless Nickel (1000 Hour Salt Spray) TZ = Aluminum Alloy, Zinc Nickel Z1 = Stainless, Passivate					
Shell Size	See Cover Dimensions Table					
Attachment Type	See Attachment Rings Style Table					
Attachment Length	In Inches					
Ring Style Dash Number	See Attachment Ring Table					

COVER DIMENSIONS

Shell Size	G DIA	H DIA MAX
11	.700 (17.78)	.940 (23.88)
13	.850 (21.59)	1.070 (27.18)
15	.975 (24.76)	1.190 (30.23)
17	1.100 (27.94)	1.320 (33.53)
19	1.207 (30.66)	1.440 (36.58)
21	1.332 (33.83)	1.570 (39.88)
23	1.457 (37.01)	1.690 (42.93)
25	1.582 (40.18)	1.820 (46.23)



ATTACHMENT RING

Style A		Style B		Style C		Style D	
Dash Number	C Dia	Dash Number	D Dia	Dash Number	E Dia	Dash Number	F Dia
085	0.265 (6.73)	08	0.468 (11.89)	50	0.425 (10.80)	01	0.140 (3.56)
095	0.312 (7.92)	10	0.593 (15.06)	52	0.485 (12.32)	02	0.182 (4.62)
100	0.391 (9.93)	12	0.718 (18.24)	54	0.640 (16.26)	03	0.191 (4.85)
101	0.516 (13.11)	14	0.844 (21.44)	56	0.750 (19.05)	04	0.197 (5.00)
102	0.583 (14.81)	16	0.968 (24.59)	58	0.890 (22.61)	05	0.167 (4.24)
103	0.641 (16.28)	18	1.093 (27.76)	60	1.015 (25.78)	06	0.125 (3.18)
104	0.708 (17.98)	20	1.187 (30.15)	62	1.095 (27.81)	07	0.218 (5.54)
105	0.766 (19.46)	22	1.343 (34.11)	64	1.130 (28.70)	09	0.156 (3.96)
106	0.896 (22.76)	24	1.484 (37.69)	66	1.250 (31.75)	00	No Eyelet
107	1.016 (25.81)	28	1.687 (42.85)	68	1.350 (34.29)	Style RL	
108	1.141 (28.98)	32	1.968 (49.99)	70	1.375 (34.92)	<p>STYLE RL SEE DRAWING 677-048</p>	
109	1.266 (32.16)	36	2.187 (55.55)	72	1.485 (37.72)		
110	1.391 (35.33)	40	2.406 (61.11)	74	1.625 (41.28)		
111	1.521 (38.63)	44	2.656 (67.46)	76	1.750 (44.45)		
112	1.641 (41.68)	48	3.031 (76.99)	78	1.875 (47.63)		
113	1.766 (44.86)			80	1.980 (50.29)		
114	1.891 (48.03)			82	2.060 (52.32)		
115	2.078 (52.78)			84	2.235 (56.77)		
116	2.406 (61.11)			86	2.310 (58.67)		
117	2.510 (63.75)			88	2.475 (62.87)		
				90	2.655 (67.44)		
				92	2.810 (71.37)		
				94	3.045 (77.34)		