

# PowerPlay™ High-Power Connectors and Cables

## SuperNine Series III PowerPlay Triple-Start 620H\*011 Saddle Clamp, General Purpose



HOW TO ORDER			
Sample Part Number	620H*011	TZ	11
Basic Part Number	620HS011 = Straight 620HA011 = 90°		
Material/Finish	C = Black Anodize M = Electroless Nickel MT = Nickel-PTFE NF = Olive Drab Cadmium ZR = Black Zinc-Nickel TZ = Tin-Zinc Body, saddles, coupling nut : aluminum Screws, washers, clinch nuts: stainless steel		
Shell Size	11, 13, 15, 17, 19, 21, 23, 25		

CONNECTOR DIMENSIONS									
Shell Size	A Thread	øB Max.	C Max	D Max	E Cable Entry		F Max.	G Max.	Screw Size
					Closed	Open			
11	M15X1.0-6H	.840 (21.3)	.88 (22.4)	.90 (22.9)	.153 (3.9)	.234 (5.9)	.786 (20.0)	.867 (22.0)	6-32
13	M18X1.0-6H	.960 (24.4)	.98 (24.9)	1.10 (27.9)	.190 (4.8)	.328 (8.3)	.979 (24.9)	.929 (24.0)	6-32
15	M22X1.0-6H	1.090 (27.7)	1.03 (26.2)	1.15 (29.2)	.260 (6.6)	.457 (11.6)	1.039 (26.4)	.992 (25.2)	6-32
17	M25X1.0-6H	1.230 (31.2)	1.13 (28.7)	1.30 (33.0)	.283 (7.2)	.614 (15.6)	1.188 (30.2)	1.056 (26.8)	6-32
19	M28X1.0-6H	1.360 (34.5)	1.38 (35.1)	1.50 (38.1)	.325 (8.3)	.634 (16.1)	1.300 (33.0)	1.233 (31.3)	8-32
21	M31X1.0-6H	1.480 (37.6)	1.48 (37.6)	1.60 (40.6)	.343 (8.7)	.698 (17.7)	1.425 (36.2)	1.296 (32.9)	8-32
23	M34X1.0-6H	1.600 (40.6)	1.63 (41.4)	1.70 (43.2)	.381 (9.7)	.823 (20.9)	1.550 (39.4)	1.358 (34.5)	8-32
25	M37X1.0-6H	1.720 (43.7)	1.73 (43.9)	1.80 (45.7)	.418 (10.6)	.853 (21.7)	1.675 (42.6)	1.420 (36.1)	8-32

SUPER NINE SERIES III POWERPLAY TRIPLE-START