

Table of Contents

<h3>Introduction</h3>		<ul style="list-style-type: none"> ■ Features and Benefits2 ■ Connector Selection Guide3 	<div style="background-color: #f4a460; padding: 5px; text-align: center;"> Selection Guide Page 3 </div>
<h3>General Information and Technical Reference</h3>		<ul style="list-style-type: none"> ■ Insert Arrangements 6-9 ■ Wire Insulation Diameters.....6 ■ Contact Design, Current Rating10 ■ Connector Materials and Finishes11 ■ Product Specification..... 12-14 ■ Material and Finish Options.....15 ■ PowerTrip® for Space Flight.....16 	<div style="background-color: #f4a460; padding: 5px; text-align: center;"> Insert Arrangements Pages 6-9 </div>
<h3>Cable Connectors Environmental</h3>		<ul style="list-style-type: none"> ■ 970-001 Plug with Accessory Thread 17 ■ 970-011 Plug with Banding Platform 19 ■ 970-005 Receptacle with Accessory Thread 21 ■ 970-033 Receptacle with Banding Platform 23 ■ Overmolded Turboflex® Cordsets 25 	
<h3>Square Flange Receptacles, Environmental</h3>		<ul style="list-style-type: none"> ■ 970-003 Square Flange Receptacle with Accessory Thread 26 ■ 970-032 Square Flange Receptacle with Banding Platform..... 28 ■ 970-009 Low Profile Square Flange Receptacle..... 30 ■ 970-013 Low Profile Square Flange Receptacle w/ O-Ring 32 ■ 970-008 Square Flange Receptacle, #8 PC Tails 34 	
<h3>Jam Nut Receptacles, Environmental</h3>		<ul style="list-style-type: none"> ■ 970-004 Jam Nut Receptacle with Accessory Thread 37 ■ 970-031 Jam Nut Receptacle with Banding Platform 39 ■ 970-010 Low Profile Jam Nut Receptacle 41 ■ 970-006 Feed-Thru Bulkhead Jam Nut Receptacle..... 43 	
<h3>Hermetic and Filter Receptacles</h3>		<ul style="list-style-type: none"> ■ 970-012 Hermetic Square Flange Receptacle 45 ■ 970-030 Hermetic Square Flange Receptacle with O-ring 47 ■ 970-038 Hermetic Receptacle with Crimp Contacts..... 49 ■ 970-025 Hermetic Jam Nut Receptacle..... 51 ■ 970-041 Lightweight Hermetic Jam Nut Receptacle 53 ■ 970-007 Hermetic Jam Nut Feed-Thru Receptacle 55 ■ 970-026 Hermetic Jam Nut Feed-Thru Receptacle w/ (2) O-rings.... 57 ■ 240-970 Filter Receptacle 59 	
<h3>Contacts and Tools</h3>		<ul style="list-style-type: none"> ■ Crimp Contacts 62 ■ Bus Bar Contacts..... 64 ■ Crimping Tools, Assembly Tools, Sealing Plugs 65 ■ Banding Tools and Straps 66 ■ Connector Holding Tools 67 	
<h3>Backshells and Accessories</h3>		<ul style="list-style-type: none"> ■ Selection Guide 68 ■ 620PS076 Strain Relief..... 69 ■ 870P001 Swing-Arm Clamp 70 ■ 310P*001 Shrink Boot Adapter..... 71 ■ 770-0035 Heatshrink Boot 72 ■ 370P*024 Environmental Backshell..... 73 ■ 380P*105 EMI Backshell 75 ■ 390P*055 EMI + Environmental Backshell 77 ■ 440P*069 EMI Banding Backshell..... 79 ■ 390PS036 Heavy Duty Backshell with Saddle Clamp..... 81 ■ 390PS086 Heavy Duty Backshell with Wire Mesh Cordgrip 82 ■ 660PS097 Protective Cover for Plug Connector..... 83 ■ 660PS098 Protective Cover for Receptacle Connector 84 ■ 780-001 Bean Rubber Cover for Plug Connector 85 ■ 780-002 Bean Rubber Cover for Receptacle Connector..... 86 ■ 930-014 Flange Gasket 87 ■ 809-532 Self-Locking Jam Nut..... 88 	<div style="background-color: #f4a460; padding: 5px; text-align: center;"> Accessories Selection Guide Page 68 </div>