

## Selection Guide: Environmental Class

SERIES™  
**795**  
 RF

**SERIES 795**

Multi-Port RF  
 Rectangular Connectors

*Precision-machined and shielded.* Series 795 connectors accommodate up to nine #8 BMB-style coax contacts. Contacts snap into connector body and are removable. Environmentally protected with fluorosilicone face seal and rear grommet. One piece connector shell provides a common ground plane and also eliminates EMI radiation through the connector. Panel mount receptacle has conductive fluorosilicone O-ring for ingress protection. #8-32 jackscrews for secure mating in high vibration environments.















### G-Link<sup>RF</sup> Contacts



18 GHz **G-Link<sup>RF</sup>** contacts have a BMB-style mating end and a female SMA interface on the back end. Attach a standard SMA plug cable to the G-Link RF contact.

- Twenty-six layouts for size #8, #12, or #16 RF contacts (sold separately)
- Unibody connector design with common ground plane
- Environmental
- Scoop-proof interface
- EMI spring available on receptacle connectors
- Snap-in, rear-release contacts

## Series 795 RF Connector Selection Guide

Cable Plugs, Socket Contacts	Cable Receptacles, Pin Contacts	Panel Mount Plugs, Socket Contacts	Panel Mount Receptacles, Pin Contacts
 <b>795-001S</b> (#8 BMB Contacts)	 <b>795-002P</b> (#8 BMB Contacts)	 <b>795-003S</b> (#8 BMB Contacts)	 <b>795-004P</b> (#8 BMB Contacts)
 <b>795-005S</b> (#12 SMPM Contacts)	 <b>795-006P</b> (#12 SMPM Contacts)	 <b>795-007S</b> (#12 SMPM Contacts)	 <b>795-008P</b> (#12 SMPM Contacts)
 <b>795-009S</b> (#16 SMPS Contacts)	 <b>795-010P</b> (#16 SMPS Contacts)	 <b>795-011S</b> (#16 SMPS Contacts)	 <b>795-012P</b> (#16 SMPS Contacts)