

GRF05 SMA-SMA Adapters

GRF05-0023 SMA MALE TO SMA FEMALE ADAPTER




SMA Male / SMA Female. GRF05-0023 connector saver adapter protects equipment from wear and tear. Stainless steel body and coupling nut, gold-plated BeCu contact, PTFE insulator, stainless steel lock ring and silicone gasket.

- Frequency range: DC - 18 GHz
- VSWR: 1.15 maximum
- Impedance: 50 ohm

PART NUMBER

GRF05-0023



GRF05-0024 SMA FEMALE TO SMA FEMALE ADAPTER




SMA Female / SMA Female. GRF05-0024 gender changer adapter connects two SMA plugs. Stainless steel body, gold-plated BeCu contact, PTFE insulator.


- Frequency range: DC - 18 GHz
- VSWR: 1.15 maximum
- Impedance: 50 ohm

PART NUMBER

GRF05-0024



GRF05-0025 SMA FEMALE TO SMA FEMALE ADAPTER, PANEL MOUNT




SMA Female / SMA Female. Jam nut panel mount. GRF05-0025 adapter connects two SMA plugs. Stainless steel body, hex nut and lock washer. Gold-plated BeCu contact, PTFE insulator, silicone O-ring.


- Frequency range: DC - 18 GHz
- VSWR: 1.15 maximum
- Impedance: 50 ohm

PART NUMBER

GRF05-0025



GRF05-0032 SMA MALE TO SMA FEMALE, 45° ANGLE




SMA Male / SMA Female. 45°. GRF05-0032 adapter has low profile coupling nut for increased clearance. Gold-plated BeCu contact. Passivated stainless steel body and coupling nut, PTFE insulator, silicone O-ring and gasket, BeCu lock ring.

- Operating temperature: -45 °C to +125 °C
- Frequency range: DC - 18 GHz
- VSWR: 1.30 maximum
- Impedance: 50 ohm


PART NUMBER

GRF05-0032



GRF05
SMA-SMA Adapters

GRF05-0031 SMA MALE TO SMA FEMALE ADAPTER, RIGHT ANGLE



SMA Male / SMA Female. GRF05-0031 90° adapter connects female SMA to male SMA. Available in six lengths. Stainless steel body and coupling nut. Gold-plated BeCu contact, PTFE insulator, BeCu lock ring. Silicone gasket and O-ring.

- Operating temperature: -45 °C to +125 °C
- Frequency range: DC - 18 GHz
- VSWR: 1.30 maximum
- Impedance: 50 ohm

PART NUMBER

Part Number	Fig.	A		B	
		In.	mm.	In.	mm.
GRF05-0031-01	Fig. 1	.626	15.9	.470	11.9
GRF05-0031-02	Fig. 2	.770	19.6	.614	15.6
GRF05-0031-03	Fig. 2	.990	25.1	.835	21.2
GRF05-0031-04	Fig. 2	1.210	30.7	1.055	26.8
GRF05-0031-05	Fig. 2	1.330	33.8	1.175	29.8
GRF05-0031-06	Fig. 2	1.670	42.4	1.514	38.5




Figure 1
GRF05-0031-01




Figure 2
GRF05-0031-02 thru -06

