

Cat6a/Cat8 Cable, #24 AWG  
963-066-24

PROTOCOL SPECIFIC

Optimized for


**El Ochito**

Cat 8 up to 40GBASE-T Ethernet



**SPEEDMASTER™**

Cat 6a up to 10GBASE-T Ethernet



**963-066-24**

- 100 Ohm twisted pair shielded cable.
- -65 to +200 °C rated operating temperature
- FEP jacket, FEP insulation
- Dual shields: Aluminized Polyimide tape and #40 AWG silver-plated copper

**NOTES**

- Cable identified with manufacturer's name and part number.
- Cable is sold in 1 foot increments. Specify desired length on purchase order.

Cable Construction		
A	(4x) Data Pairs	100 Ohm (Nom.), Shielded Twisted Pair
	Conductors	24 AWG (19/36) High Strength Copper Alloy
	Insulation	FEP
	Colors	Blue, White/Blue Orange, White/Orange Green, White/Green Brown, White/Brown
	Binder	PTFE Tape
	Pair Shield	Aluminum/Polyimide tape
B	Outer Shield	Silver Plated Copper, 90% min. coverage
C	Outer Jacket	FEP (White Laser-Markable)
Minimum bend radius: 1.25		
Weight: 19.0 g/ft		

Electrical Performance	
Dielectric Withstanding Voltage (VRMS)	600
Differential Impedance	100 ± 10 Ohms
Insertion Loss (SDD21)	See Table 1

Environmental Properties	
Temperature Range	-65°C to 200°C

Table 1: Attenuation		
Frequency (MHz)	dB / ft Typical	dB / ft Maximum
100	.062	.081
250	.104	.125
500	.153	.182
1000	.227	.266
2000	.330	.380