

MISSION-CRITICAL
INTERCONNECT
SOLUTIONS



Glenair
SIGNATURE SERIES

STAR-PAN II Soldier Data / Power Hub

For Improved Tactical Squad Situational Awareness





STAR-PAN™ II

Integrated USB data/power distribution hub for fast-moving special operation forces and small-squad team leaders

Mission flexibility is key in meeting the warfighter's ever-evolving duties in the field. The STAR-PAN™ II USB data/power hub is designed for just the most core C4ISR capabilities including End User Device (EUD) integration, radio comm support, video downlink (Rover) as well as robust management of battery and auxiliary power sources. Two versions are available: a pre-cabled hub assembly with integrated EUD and power cables equipped with NATO STANAG 4695 standard connectors; and a connectorized hub, ready for configuration with customer-specified cables and adapters.

KEY FEATURES/BENEFITS

- Provides battery power and +5VBus power via 2 cabled power input ports for extended missions or battery hot swap
- Supports soldier EUD/Host, Radio, and up to 2 USB peripheral devices (with bifurcated 808-081 cable for 2nd device)
- SMBus, USB2.0 (full and high-speed), USB1.1 compatible interface
- Power monitoring and management for each voltage rail and port
- Compatible Personal Area Network (PAN) pin configuration and Smart Battery interface
- Built-in SMBus to USB converter to USB host devices

FEATURES

- STAR-PAN II 808-057-1 with integrated cables, or 808-194 standard hub
- Designated host/EUD port, designated radio/peripheral port, and Universal PAN compliant port (expandable for up to two devices)
- Supports hot-swappable power sources and radio-supplied backup power
- Heat-efficient electronics packaging to optimize efficiency and extend battery life

PAN APPLICATIONS

- Dismounted infantry soldier situational awareness and battery management
- Fast-moving special operations forces communications and situational awareness
- Fire rescue field communications and logistics
- Underground, highwall, and surface mining wireless communications

Export of STAR-PAN™ USB Hub/Power Distribution systems is restricted and/or controlled by U.S. Department of Commerce Export Administration Regulations

WARFIGHTER TOUGH

STAR-PAN™ II



808-194 / 808-057 -1

2 port (expandable) power and data hub / cabled hub assembly

OVERVIEW

The Glenair STAR-PAN™ II Hub is a lightweight, durable, compact data and power distribution hub, ruggedized for harsh environment dismounted soldier applications. STAR-PAN II provides a data backplane for up to 3 USB devices with power monitoring and management for connected external peripherals, radio, and the soldier's EUD/Host. STAR-PAN II is compatible with USB1.1, USB2.0 (full and high-speed), and SMBus protocols, and incorporates dual power input ports for extended missions or battery substitution, minimizing down time. All connector interfaces are compliant to the NATO STANAG 4695 standard for Soldier Power Connectors. Recommended: general-purpose C1 cable for EUD, battery, and peripheral connectivity.

PERFORMANCE SPECIFICATIONS

Operating Conditions	
Operating Temperature	-40°C to +55°C
Storage Temperature	-40°C to +80°C
Operation Altitude	9754m
Storage Altitude	15240m
Water Immersion, Mated	MIL-STD-810, Method 512, 1m for 1 hr.; IP67 rated dust / water resistant
Host & Pan	
Battery Voltage	10.0V to 20.0V, 14.8V typical
Battery Supply Current	3.5A Maximum per individual port
Battery Supply Total Current	5A total system
5VUSB Supply Voltage	4.75V to 5.1 V, 4.90V typical
5VUSB Supply Current	3A Maximum per individual port
Radio Port	
Battery Voltage	10.0V to 20.0V, 14.8V typical. Highest priority for power management
Battery Supply Current	5A maximum per individual port
+5V Back Up Supply Current	1.2A typical, 3A max, based on radio supply, radio 1 primary
+5V Back Up Supply Current	.5A per port
Battery Port	
Battery Input Voltage	10V to 20V
Battery Supply Current	5A maximum system supply current
SMBus Data	-0.5V to +3.5V, 808-194 P5 only

STAR-PAN™ HUBS + ACCESSORIES


HOW TO ORDER

Sample Part Number:

808-194

STAR-PAN Hub

STAR-PAN II 2 port power/data hub
[NATO NSN 5935-01-691-2366]



STAR-PAN II PORT CONFIGURATION

EUD	1
RADIO	1
PAN	1
POWER	2

Both versions of STAR-PAN II provide identical capabilities. Non-cabled version is designed more for users with unique EUD or battery-power configuration requirements. All cables supplied separately.


HOW TO ORDER: HUB / CABLE ASSEMBLY VERSION

Sample Part Number:

808-057-1

Hub with Integrated Cables

STAR-PAN II 2 port power/data hub with integrated cables
[NATO NSN 6140-01-682-5677]



Rev. 10.09.20

WARFIGHTER TOUGH

STAR-PAN™ II



808-057-1 and 808-194 Configuration diagram 2 port (expandable) power and data system


STAR-PAN II CAPABILITY DIAGRAM

- Universal PAN compliant ports (up to two devices)
- 1 designated host/EUD port
- 1 designated radio peripheral port
- 1 expandable PAN port for up to two USB peripherals
- Hot-swappable power sources
- Radio-supplied backup power
- Glenair power port management

SPECIFICATIONS

■ Across-the-board support for all soldier radio types:

- L3HARRIS [AN/PRC-117G, AN/PRC-152A]
- THALES [AN/PRC-154 Rifleman, AN/PRC-148 JEM]
- Domo Tactical Communications (DTC) [SOL8SDR-H]
- ELBIT [PNR-1000, MCTR-7200HH]
- Silvus Technologies [SC4200, SC4400]
- Bittium [Tough SDR Handheld™]



WARFIGHTER TOUGH


STAR-PAN™ II



808-057-1 and 808-194 Configuration diagram 2 port (expandable) power and data system


GLENAIR STAR-PAN TECHNOLOGY ILLUSTRATED IN THIS CAPABILITY DIAGRAM

STAR-PAN Component Description	Part Number
STAR-PAN II Multiport USB and Power Distribution Hub	808-057-1
STAR-PAN Expansion Cable	808-081
PRC 152A Radio Data Adapter	808-032
DAGR GPS/Navigation Cable	808-040
PLRF 15C/25C Laser Range Finder Cable	808-049
TacROVER-P SIR 2.0 ISR Receiver Cable	808-045
TacROVER-E ISR Receiver Cable	808-043
Tactical Net Rover ISR Receiver Cable	808-117
USB 2.0 Adapter Cable	808-053
Hand-Held Radio Battery Adapter	808-066
BA5590/BB2590 Battery Shoe	808-048
Radio Power Booster	TS3-022
STAR-PAN II Quick-Start User's Guide	990-TS002




Pocket-Size
STAR-PAN II
Quick-Start
User's Guide


STAR-PAN™ HUBS + ACCESSORIES




End User Device*




808-175
Battery Adapter
PRC-152A,
PRC-152,
and PRC-148 Radios



808-048 Battery Shoe
for BA5590 / BB2590
Batteries




808-242
Charging Battery Adapter
for BB2590 Batteries



Conformal Wearable Battery*
(direct connection, no adapter required)

* Example compatible devices, not supplied by Glenair



MISSION-CRITICAL INTERCONNECT SOLUTIONS

Glenair, Inc.

1211 Air Way • Glendale, California • 91201-2497

Telephone: 818-247-6000 • Fax: 818-500-9912 • sales@glenair.com

www.glenair.com

Glenair Power Products Group

20 Sterling Drive
Wallingford, CT
06492

Telephone:
203-741-1115
Facsimile:
203-741-0053
sales@glenair.com

Glenair UK Ltd

40 Lower Oakham Way
Oakham Business Park
Mansfield, Notts
NG18 5BY England

Telephone:
+44-1623-638100
Facsimile:
+44-1623-638111
sales@glenair.co.uk

Glenair Microway Systems

7000 North Lawndale Avenue
Lincolnwood, IL
60712

Telephone:
847-679-8833
Facsimile:
847-679-8849

Glenair Nordic AB

Gustav III : S Boulevard 46
SE-169 27 Solna
Sweden

Telephone:
+46-8-50550000
sales@glenair.se

Glenair GmbH

Schaberweg 28
61348 Bad Homburg
Germany

Telephone:
06172 / 68 16 0
Facsimile:
06172 / 68 16 90
info@glenair.de

Glenair Iberica

C/ La Vega, 16
45612 Velada
Spain

Telephone:
+34-925-89-29-88
Facsimile:
+34-925-89-29-87
sales@glenair.es

Glenair Italia S.p.A.

Via Del Lavoro, 7
40057 Quarto Inferiore –
Granarolo dell'Emilia
Bologna, Italy

Telephone:
+39-051-782811
Facsimile:
+39-051-782259
info@glenair.it

Glenair France SARL

7, Avenue Parmentier
Immeuble Central Parc #2
31200 Toulouse
France

Telephone:
+33-5-34-40-97-40
Facsimile:
+33-5-61-47-86-10
sales@glenair.fr

Glenair Korea

B-1304 Gunpo IT Valley
148 Gosan-Ro, Gunpo-Si
Kyunggi-Do, Korea
435-733

Telephone:
+82-31-8068-1090
Facsimile:
+82-31-8068-1092
sales@glenair.kr