

MISSION-CRITICAL
INTERCONNECT
SOLUTIONS



Glenair
SIGNATURE SERIES

STAR-PAN VI Soldier Data / Power Hub

For Advanced JTAC / DACAS Fires Control





STAR-PAN™ VI

Integrated USB data/power distribution hub for digitally aided close air support (DACAS) and other combined mission commander / JTAC applications

KEY FEATURES/BENEFITS

- Battery Power and +5VBus power to up to 4 USB devices, 2 dedicated Radio ports
- Robust fault mode protection circuitry for surge, reverse voltage, and over current
- Embedded level 3 charge control circuitry for smart battery interface, within a wide charge voltage range
- Compatible with DC power sources
- APS port for system power and main system battery charging on extended missions
- Radio Port Vbus System Hold Up for extended mission time and weight reduction
- Compatible Personal Area Network (PAN) pin configuration and Smart battery interface
- Built-in SMBus to USB converter to USB host device

FEATURES

- Universal PAN compliant ports (up to six devices)
- 1 designated host/EUD port
- 2 designated radio peripheral ports
- 4 PAN receptacles for up to four peripherals
- Battery and auxiliary power source input
- Glenair power port management
- Radio-supplied backup power
- Smart battery charging from auxiliary power
- Up to 5A battery power per port, 5A system total
- Up to 3A 5 Volt VBUS power per port, 5A system total
- Precision-machined construction, integrated connectors
- Heat-efficient electronics packaging to optimize efficiency and extend battery life



808-037

6 port smart power and data hub system

OVERVIEW

The Glenair STAR-PAN™ VI Hub is a lightweight, durable, compact data and power distribution hub, ruggedized for harsh environment dismounted soldier applications. The connectorized hub provides a data backplane with power monitoring and management to connected external peripherals used in Digitally Aided Close Air Support (DACAS) and other mission applications. The hub is compatible with USB1.1, USB2.0 (full and high speed), and SMBus protocols. STAR-PAN™ VI contains two power inputs for extended missions. Two radio ports capable of powering up the USB Data backplane and host connection. A dedicated charge port for use with smart batteries and auxiliary power sources including multiple DC power sources such as vehicle power, solar panels, kinetic energy devices or fuel cells. All connector interfaces compliant to NATO STANAG 4695. Recommended: general-purpose C1 cable for EUD, battery, and peripheral connectivity.

HOW TO ORDER IS

Sample Part Number:

808-037

Connectorized Hub

STAR-PAN VI 6-port power/data hub


Port Configuration: 1 EUD, 2 RADIO, 4 PAN, 2 POWER

PERFORMANCE SPECIFICATIONS

Operating Conditions	
Operating Temperature	-40°C to +55°C
Storage Temperature	-40°C to +80°C
Operation Altitude	9754m
Storage Altitude	15240m
Water Immersion, Mated	MIL-STD-810, Method 512, 1m for 1 hr.; IP67 rated dust / water resistant
Host & Pan 1-4	
Battery Voltage	10.0V to 20.0V, 14.8V typical
Battery Supply Current	5A Maximum per individual port
+5V Backup Total Supply Current	5A based on radio supply, Radio 1 primary
Radio 1 and 2 Ports	
Battery Voltage	10.0V to 20.0V, 14.8V typical. Highest priority for power management
Battery Supply Current	5A maximum per individual port
+5V Back Up Supply Current	1.2A typical, 3A max, based on radio supply, radio 1 primary
+5V Back Up Supply Current	.5A per port
Auxiliary Power Supply Port	
Auxiliary Voltage Source	10V to 36V
Auxiliary Supply Current	5 A maximum system supply current
Battery Port	
Battery Input Voltage	10V to 20V
Battery Supply Current	5A maximum system supply current
Battery Charge Current	3A

PAN APPLICATIONS

- JTAC Digitally Aided Close Air Support (DACAS)
- Tactical ops center operations commander






808-037 6 port smart power and data system Configuration diagram

STAR-PAN VI CAPABILITY DIAGRAM

SPECIFICATIONS

- Universal PAN compliant ports (up to six devices)
- 1 designated host/EUD port
- 2 designated radio peripheral ports
- 4 PAN receptacles for up to four peripherals
- Battery and auxiliary power source input
- Glenair power port management
- Radio-supplied backup power
- Smart battery charging from auxiliary power
- Up to 5A battery power per port, 5A system total
- Up to 3A 5 Volt VBUS power per port, 5A system total





808-037 6 port smart power and data system Configuration diagram


GLENAIR STAR-PAN TECHNOLOGY ILLUSTRATED IN THIS CAPABILITY DIAGRAM

STAR-PAN Component Description	Part Number
STAR-PAN VI Multiport USB and Power Distribution Hub	808-037
STAR-PAN General-Purpose Extension Cable	808-047
DAGR GPS/Navigation Cable	808-040
RT-1922 MicroLight SADL Radio Cable	808-044
PRC 152A Radio Data Adapter	808-032
TacROVER-E ISR Receiver Cable	808-043
TacROVER-P SIR 2.0 ISR Receiver Cable	808-045
Tactical Net Rover ISR Receiver Cable	808-117
PLRF 15C/25C Laser Range Finder Cable	808-049
USB 2.0 Adapter Cable	808-053
Hand-Held Radio Battery Adapter	808-066
BA5590/BB2590 Battery Shoe	808-048
Radio Power Booster	TS3-022
AC/DC Power Adapter Cable	808-064
STAR-PAN VI Quick-Start User's Guide	990-TS003




Pocket-Size
STAR-PAN VI
Quick-Start
User's Guide

STAR-PAN™ HUBS + ACCESSORIES



* Example compatible devices, not supplied by Glenair



MISSION-CRITICAL INTERCONNECT SOLUTIONS

Glenair, Inc.

1211 Air Way • Glendale, California • 91201-2497

Telephone: 818-247-6000 • Fax: 818-500-9912 • sales@glenair.com

www.glenair.com

Glenair Power Products Group

20 Sterling Drive
Wallingford, CT
06492

Telephone:
203-741-1115
Facsimile:
203-741-0053
sales@glenair.com

Glenair UK Ltd

40 Lower Oakham Way
Oakham Business Park
Mansfield, Notts
NG18 5BY England

Telephone:
+44-1623-638100
Facsimile:
+44-1623-638111
sales@glenair.co.uk

Glenair Microway Systems

7000 North Lawndale Avenue
Lincolnwood, IL
60712

Telephone:
847-679-8833
Facsimile:
847-679-8849

Glenair Nordic AB

Gustav III : S Boulevard 46
SE-169 27 Solna
Sweden

Telephone:
+46-8-50550000
sales@glenair.se

Glenair GmbH

Schaberweg 28
61348 Bad Homburg
Germany

Telephone:
06172 / 68 16 0
Facsimile:
06172 / 68 16 90
info@glenair.de

Glenair Iberica

C/ La Vega, 16
45612 Velada
Spain

Telephone:
+34-925-89-29-88
Facsimile:
+34-925-89-29-87
sales@glenair.es

Glenair Italia S.p.A.

Via Del Lavoro, 7
40057 Quarto Inferiore –
Granarolo dell'Emilia
Bologna, Italy

Telephone:
+39-051-782811
Facsimile:
+39-051-782259
info@glenair.it

Glenair France SARL

7, Avenue Parmentier
Immeuble Central Parc #2
31200 Toulouse
France

Telephone:
+33-5-34-40-97-40
Facsimile:
+33-5-61-47-86-10
sales@glenair.fr

Glenair Korea

B-1304 Gunpo IT Valley
148 Gosan-Ro, Gunpo-Si
Kyunggi-Do, Korea
435-733

Telephone:
+82-31-8068-1090
Facsimile:
+82-31-8068-1092
sales@glenair.kr