



470-015 StarShield™ EMI/RFI Shield Termination Backshell for MIL-DTL-38999 Series III and IV Connectors



Environmental

Rear End
OptionsSelf
LockingStandard
LengthHigh
Ferrule Count

StarShield™ environmental, backshell with self-locking coupling nut and shrink boot

Product Series
470 -
StarShield™

470

**Angular
Function**

S - Straight
H - 45°
J - 90°

H

S

Finish Code
(See Table II)

015

**Ferrule
Quantity Code**
(See Table I)

17

Drilled Star
DS - Drilled Star -
Optional
(Omit if Not Required)
(See Note 4)

6

G

DS

- T

Connector Designator
H - MIL-DTL-38999
Series III and IV






**Basic
Number**

**Order
Number**
(See Table I)

Rear End Options

B - Compression Nut
with Band
C - Conduit Adapter
G - Gland Nut
T - Tinel Nut with Tinel
Ring for Single Braid

Shrink Boot
T - Shrink Boot -
Optional
(Omit for None)
(See Table III)



Dimensions in inches (millimeters) and are subject to change without notice.

© 2012 Glenair, Inc.

StarShield™ Zero Length Shield Termination Catalog

CAGE Code 06324

Printed in U.S.A.

GLENAIR, INC. • 1211 AIR WAY • GLENDALE, CA 91201-2497 • 818-247-6000 • FAX 818-500-9912

www.glenair.com

B-14

E-Mail: sales@glenair.com

470-015

StarShield™ EMI/RFI Shield Termination Backshell for MIL-DTL-38999 Series III and IV Connectors



Table I: Dimensions							
Order No.	Connector Shell Size Ref	A Thread ISO Metric	B Dia Max	C Dia Max	D Max	E Max	F Max
09	A/9	M12 X 1 - 6H	.940 (23.9)	.690 (17.5)	.750 (19.1)	1.000 (25.4)	.880 (22.4)
11	B/11	M15 X 1 - 6H	1.060 (26.9)	.850 (21.5)	.780 (19.8)	1.020 (26.0)	.960 (24.4)
13	C/13	M18 X 1 - 6H	1.170 (29.7)	.890 (22.5)	.810 (20.6)	1.040 (26.5)	1.000 (25.4)
15	D/15	M22 X 1 - 6H	1.290 (32.8)	1.000 (25.4)	.830 (21.1)	1.080 (27.5)	1.070 (27.2)
17	E/17	M25 X 1 - 6H	1.420 (36.1)	1.120 (28.5)	.860 (21.8)	1.100 (28.0)	1.130 (28.7)
19	F/19	M28 X 1 - 6H	1.540 (39.1)	1.240 (31.5)	.880 (22.4)	1.120 (28.5)	1.180 (30.0)
21	G/21	M31 X 1 - 6H	1.670 (42.4)	1.380 (35.0)	.910 (23.1)	1.140 (29.0)	1.250 (31.8)
23	H/23	M34 X 1 - 6H	2.010 (51.1)	1.500 (38.0)	.930 (23.6)	1.180 (30.0)	1.310 (33.3)
25	J/25	M37 X 1 - 6H	2.120 (53.8)	1.610 (41.0)	.940 (23.9)	1.220 (31.0)	1.360 (34.5)

Table I: Dimensions (Continued)						
Order No.	G Max	H ±.003 (.08)	J Thread ISO Metric	K ±.004 (.10)	Ferrule Quantity (See Note 4)	
					Std.	Opt.
09	1.140 (29.0)	.435 (11.0)	M12 X 1 - 6g	.315 (8.00)	1	-
11	1.200 (30.5)	.623 (15.8)	M15 X 1 - 6g	.531 (13.5)	2	-
13	1.260 (32.0)	.746 (18.9)	M18 X 1 - 6g	.591 (15.0)	3	-
15	1.320 (33.5)	.871 (22.1)	M22 X 1 - 6g	.709 (18.0)	5	-
17	1.380 (35.0)	.996 (25.3)	M25 X 1 - 6g	.827 (21.0)	6	7
19	1.440 (36.5)	1.121 (28.5)	M28 X 1 - 6g	.945 (24.0)	7	-
21	1.520 (38.5)	1.245 (31.6)	M31 X 1 - 6g	1.063 (27.0)	9	11
23	1.570 (40.0)	1.371 (34.8)	M34 X 1 - 6g	1.181 (30.0)	10	13
25	1.630 (41.5)	1.371 (34.8)	M37 X 1 - 6g	1.299 (33.0)	12	17


Table II: Material and Finish Options	
Code	Material; Finish Description
M	Aluminum; electroless nickel
MT	Aluminum; nickel - PTFE
NF	Aluminum; CAD/O. D. over electroless nickel
ZN	Aluminum; zinc nickel/O. D. over electroless nickel
ZR	Aluminum; zinc nickel/black over electroless nickel (RoHS)
ZRC	Aluminum; zinc nickel over electroless nickel (RoHS)
Z1	Stainless steel; passivate
ZM	Stainless steel; electroless nickel

Table III: Shrink Boot	
Shell Size	Shrink Boot Part Number
09	770-001S1 04
11	770-001S1 06
13	770-001S1 06
15	770-001S1 07
17	770-001S1 07
19	770-001S1 08
21	770-001S1 08
23	770-001S1 08
25	770-001S1 09

Material/Finish	
Backshell, elbows, coupling and gland nut, compression ring and star	Aluminum alloy or CRES/Table II
Anti-decoupling device	Corrosion resistant material
Tinel ring	Nickel-titanium alloy/n.a.
Band	CRES/passivate

Notes:

1. Assembly identified with manufacturer's name, part number and date code, space permitting.
2. For effective grounding, connector with conductive finish should be used.
3. Glenair 600 Series Backshell Assembly Tools are recommended for assembly and installation.
4. Star not supplied with order number 09. Drilled star is available on order numbers 15-25 only. If optional ferrule quantity per Table I is selected, one split and one solid star will be supplied.
5. Over-travel coupling design provides self-seating and self-locking functionality, eliminating lock-wire requirements.
6. Ferrule kit sold separately.
687-764 ferrule and HST device kit
687-809 ferrule and sealing device kit
687-748 solder ferrule
687-841-01 HST flex device



Dimensions in inches (millimeters) and are subject to change without notice.