


MIL-DTL-38999 Series I Type

870F001 Swing-Arm® saddle clamp

BACKSHELLS AND ACCESSORIES



Shell Size	A Thread UNEF-2B	øB Min	C Max	D Flats	E Max	F Max	G Max	H Max	J Max	K Ref.
8/9	0.4375-28	.264 (6.71)	.812 (20.62)	.750 (19.05)	1.43 (36.32)	1.35 (34.29)	.78 (19.81)	.91 (23.11)	.87 (22.10)	.393 (9.98)
10/11	0.5625-24	.392 (9.96)	.938 (23.83)	.875 (22.23)	1.50 (38.10)	1.45 (36.83)	.87 (22.10)	.94 (23.88)	.96 (24.38)	.455 (11.56)
12/13	0.6875-24	.506 (12.85)	1.125 (28.58)	1.000 (25.40)	1.56 (39.62)	1.60 (40.64)	.97 (24.64)	1.12 (28.45)	1.03 (26.16)	.598 (15.19)
14/15	0.8125-20	.631 (16.03)	1.250 (31.75)	1.125 (28.58)	1.57 (39.88)	1.68 (42.67)	1.02 (25.91)	1.21 (30.73)	1.10 (27.94)	.710 (18.03)
16/17	0.9375-20	.756 (19.20)	1.375 (34.92)	1.250 (31.75)	1.66 (42.16)	1.78 (45.21)	1.09 (27.69)	1.29 (32.77)	1.16 (29.46)	.839 (21.31)
18/19	1.0625-18	.844 (21.44)	1.500 (38.10)	1.375 (34.92)	1.66 (42.16)	1.86 (47.24)	1.14 (28.96)	1.39 (35.31)	1.22 (30.99)	.934 (23.72)
20/21	1.1875-18	.970 (24.64)	1.625 (41.28)	1.500 (38.10)	1.81 (45.97)	2.02 (51.31)	1.24 (31.50)	1.50 (38.10)	1.29 (32.77)	1.068 (27.13)
22/23	1.3125-18	1.094 (27.79)	1.750 (44.45)	1.625 (41.28)	1.84 (46.74)	2.09 (53.09)	1.30 (33.02)	1.57 (39.88)	1.36 (34.54)	1.197 (30.40)
24/25	1.4375-18	1.219 (30.96)	1.875 (47.63)	1.750 (44.45)	2.00 (50.80)	2.20 (55.88)	1.45 (36.83)	1.64 (41.66)	1.55 (39.37)	1.323 (33.60)