




RUGGED REVERSE-BAYONET Super ITS-ITH Octobyte™ High-Speed Ethernet Connectors




Contacts and Standard Insert Arrangements

Series ITS - ITH Octobyte™ Connectors

Precision machined connectors with hybrid insert arrangement offering Octobyte contacts for data and power contacts provide both network connectivity and power distribution in one connector. Designed for extreme environmental exposure and corrosion resistance typically needed in rail, mining, and other industrial applications. Convenient reverse bayonet mating provides easy intermateability while the locking three pin bayonet coupler prevents the connector from demating under high shock and high vibration conditions. Accessory thread for attachment of backshells and adapters.



03 - Plug



030 - Rear Panel-mount Wall-mount Receptacle

		How To Order								
Sample Part Number:		ITH	Ø3Ø	R	5C	32Q4	S	BØ	NØ	F7
Series	ITH									
Contact Size	030 = rear panel mount, wall mount receptacle 06 = straight plug									
Environmental	R = environmental									
Number of Keys	5C = 5 keys									
Insert Arrangements	28-OB4, 36-OB7									
Contact Gender	P = pin contacts (male) S = socket contacts (female)									
Connector less contact	BØ = contact not supplied (order the contact separately)									
Accessory	NØ = without backshell. Please consult the factory for options									
Plating	F6 = electrodeposited black paint (cataphoresis), RoHS compliant F7 = black zinc nickel, RoHS compliant									

FRONT VIEW PLUG CONNECTORS



28-OB4
2 OCTOBYTE
2 SIZE 8 CONTACTS



36-OB7
3 OCTOBYTE
4 SIZE 8 CONTACTS

SUPER ITS: HIGH-SPEED, HIGH DATA-RATE

B