




LIGHTWEIGHT, LOW RESISTANCE



“Mission-Critical” hermetic sealing with 1×10^{-7} leak-rate performance

Hermetically-sealed interconnects used in vacuum or high-altitude applications prevent moisture and other contaminants from damaging sensitive electronic equipment. Glass-to-metal hermetic sealing has been the gold standard in the aerospace and petrochemical industries for decades due to the strength and long-term durability of the materials used. But glass-to-metal seal hermetics come with a big price tag in both weight and electrical resistance.

CODE RED is an innovative sealing encapsulant and application process—invented by Glenair—that provides durable hermetic sealing in a lightweight aluminum package. CODE RED allows for the use of conventional gold-plated copper alloy contacts, significantly improving electrical performance. CODE RED hermetic connectors are available now in Glenair SuperNine® (D38999 Series III type), Series 80 Mighty Mouse, and M24308 D-Sub. These connectors deliver reliable, life-of-system 1×10^{-7} max leak-rate hermetic sealing and special non-magnetic (zero residual magnetism) versions are also available, consult factory.



- Full hermetic sealing, with 1×10^{-7} in a lightweight aluminum shell and low electrical resistance, gold-plated copper contacts
- Meets NASA aerospace temperature and corrosion resistance standards.
- Meets ASTM-E595 outgassing requirements when ordered with modification code 683
- Operating temperature -65°C to $+200^{\circ}\text{C}$
- Available today in Mighty Mouse 806 Mil-Aero, M24308/9 D-Sub and D38999/23 glass-to-metal seal hermetics
- Significant weight savings—up to +50%
- Order-of-magnitude improvement in current carrying capacity and electrical resistance compared to Kovar/Inconel solutions