


MIL-DTL-38999 Series III Type

Non-Standard contact arrangements


SA1234-13L-26



Contact Id	Location		Contact Size
	X Axis	Y Axis	
A	0.000	+0.137	No. 22
B	+0.097	+0.171	No. 22
C	+0.097	-0.171	No. 22
D	0.000	-0.137	No. 22
E	-0.097	-0.171	No. 22
F	-0.097	+0.171	No. 22
1	+0.128	0.000	No. 12
2	-0.128	0.000	No. 12


"L" Indicates Special Arrangement.

SA1234-21L-48



Contact Id	Location		Contact Type
	X Axis	Y Axis	
A	0.000	+0.254	8 GA
B	+0.254	0.000	8 GA
C	0.000	-0.254	8 GA
D	-0.254	0.000	8 GA

SA1234-15L-04



Contact Id	Location		Contact Size
	X Axis	Y Axis	
A	+0.125	+0.125	No. 12
B	+0.125	-0.125	No. 12
C	-0.125	-0.125	No. 12
D	-0.125	+0.125	No. 12


"L" Indicates Special Arrangement.

REFERENCE MATERIAL

MIL-DTL-38999 Series III Type

Non-Standard contact arrangements

SA1234-25L-66



Contact Id	Location		Contact Type
	X Axis	Y Axis	
1	0	0.519	22D GA
2	0.106	0.519	
3	0.212	0.519	
4	0.371	0.426	
5	0.442	0.346	
6	0.499	0.255	16 GA
7	0.501	0.115	
8	0.562	-0.010	22D GA
9	0.550	-0.107	
10	0.493	-0.270	
11	0.437	-0.357	12 GA
12	0.362	-0.428	
13	0.197	-0.450	22D GA
14	0.057	-0.557	
15	0.057	-0.557	12 GA
16	-0.197	-0.450	
17	-0.362	-0.428	22D GA
18	-0.437	-0.357	
19	-0.493	-0.270	
20	-0.550	-0.107	
21	-0.562	-0.010	
22	-0.501	0.115	16 GA


Contact Id	Location		Contact Type
	X Axis	Y Axis	
23	-0.499	0.255	22D GA
24	-0.442	0.346	
25	-0.371	0.426	
26	-0.212	0.519	
27	-0.106	0.519	
28	0.053	0.432	
29	0.159	0.432	
30	0.265	0.432	
31	0.318	0.344	
32	0.388	0.255	
33	0.472	-0.170	
34	0	-0.464	
35	-0.472	-0.170	
36	-0.388	0.255	
37	-0.318	0.344	
38	-0.265	0.432	
39	-0.159	0.432	
40	-0.053	0.432	
41	0	0.344	
42	0.106	0.344	
43	0.212	0.344	
44	0.394	-0.034	16 GA

Contact Id	Location		Contact Type
	X Axis	Y Axis	
45	0.305	-0.232	12 GA
46	0.053	-0.347	22D GA
47	-0.053	-0.347	
48	-0.305	-0.232	12 GA
49	-0.394	-0.034	16 GA
50	-0.212	0.344	22D GA
51	-0.106	0.344	
52	0.053	0.257	
53	0.159	0.257	16 GA
54	0.265	0.257	
55	0.273	0.120	
56	0.182	-0.032	
57	0.091	-0.184	
58	-0.091	0.184	22D GA
59	-0.182	-0.032	
60	-0.273	0.120	
61	-0.265	0.257	22D GA
62	-0.159	0.257	
63	-0.053	0.257	16 GA
64	0.091	0.120	
65	0	-0.032	
66	-0.091	0.120	

MIL-DTL-38999 Series III Type

Non-Standard contact arrangements

SA1234-23L-54



Contact Id	Location	
	X Axis	Y Axis
1	0.142	0.461
2	0.226	0.422
3	0.301	0.372
4	0.372	0.301
5	0.422	0.226
6	0.461	0.142
7	0.461	-0.142
8	0.422	-0.226
9	0.372	-0.301
10	0.301	-0.372
11	0.226	-0.422
12	0.142	-0.461
13	-0.142	-0.461
14	-0.226	-0.422
15	-0.301	-0.372
16	-0.372	-0.301
17	-0.422	-0.226
18	-0.461	-0.142
19	-0.461	0.142
20	-0.422	0.226
21	-0.372	0.301
22	-0.301	0.372
23	-0.226	0.422
24	-0.142	0.461
25	0.000	0.378
26	0.162	0.353
27	0.239	0.306

Contact Id	Location	
	X Axis	Y Axis
28	0.306	0.239
29	0.353	0.162
30	0.378	0.000
31	0.353	-0.162
32	0.306	-0.239
33	0.239	-0.306
34	0.162	-0.353
35	0.000	-0.378
36	-0.162	-0.353
37	-0.239	-0.306
38	-0.306	-0.239
39	-0.353	-0.162
40	-0.378	0.000
41	-0.353	0.162
42	-0.306	0.239
43	-0.239	0.306
44	-0.162	0.353
45	0.000	0.172
46	0.172	0.172
47	0.172	0.000
48	0.172	-0.172
49	0.000	-0.172
50	-0.172	-0.172
51	-0.172	0.000
52	-0.172	0.172
53	0.000	0.000

"L" Indicates Special Arrangement.