

SuperNine® USB 3.0 type A

MIL-DTL-38999 Series III Type connectors

233-0450 USB 3.0 Cable Assembly



USB 2.0 AND 3.0 CONNECTORS



2330-0450 Glenair SuperSeal™ USB 3.0 plug cable jumper, with active repeater.

SuperSeal USB cable assemblies with IP67 open face rated connectors offer complete protection from environmental debris and water ingress common under harsh environmental conditions. USB 3.0 can be ordered in horizontal or vertical orientation to provide further security against mis-mating and conforms to existing USB orientations. Additional length options and custom configurations available. Please consult factory.

All external dimensions, features, etc. compliant with D38999/20, /24, &/26. Consult factory for additional information.

Material and Finish	
NF	Aluminum/cadmium, olive drab
ME	Aluminum/electroless nickel
ZR	Zinc nickel, black (tri-valent chromium) RoHS compliant

NOTES

1. Meets IP67 in unmated condition, IP68 mated
2. SuperSeal plug houses USB plug.

Part Number Development								
Sample Part Number	2330-0450	NF	G6	-15	3	A	N	H -03
Basic Number	2330-0450							
P1 Finish	See Material and Finish table							
P1 Connector Style ¹	G6 = Plug							
P1 Shell Size	15							
USB Performance	3 = USB 3.0							
USB Interface	A = Type A							
Polarization	A, B, C, D, E, N = Normal							
USB Orientation	H = Horizontal V = Vertical							
Overall Length	01 thru 10; length in feet.							

