



USB 2.0 TYPE A

# Series IPT (26482 Type) Bayonet Coupler




IPT340 Coupler with Accessory Threads and USB Male-to-Female (Plug) or Female-to-Female (Receptacle)

G




How to Order							
Sample Part Number	IPT340 00 16 2 A H F6						
Basic Number	IPT340						
Connector Style <sup>1</sup>	06 = Plug 01 = In-Line Receptacle 070 = Rear Panel Mount Jam Nut Receptacle 00 = Wall Mount Receptacle						
Shell Size	16						
USB Performance	2 = 2.0						
USB Type	A = Type A						
Orientation Option	H = Horizontal    V = Vertical						
Material/Finish	Omit for Aluminum/Cadmium, Olive Drab F6 = Black Polymer Electrocoat F7 = Conductive Black Zinc Nickel F11 = Electroless Nickel						

### USB Orientation Options



### 06 - PLUG WITH ACCESSORY THREADS



### NOTES

1. See Section A panel cutout dimensions



USB 2.0 TYPE A


# Series IPT (26482 Type) Bayonet Coupler




IPT340 Coupler with Accessory Threads and USB Male-to-Female (Plug) or Female-to-Female (Receptacle)



## 01 - INLINE RECEPTACLE WITH ACCESSORY THREADS



## 070 - REAR PANEL MOUNT JAM NUT RECEPTACLE WITH ACCESSORY THREADS



## 00 - WALL MOUNT RECEPTACLE WITH ACCESSORY THREADS

