



RJ45 CAT 5E ETHERNET

# Series ITS (5015 type) Reverse-Bayonet




ITS301 Connector with Accessory Threads and Plug (Plug) or Jack (Receptacle) to Crimp Removable Contacts



How to Order							
<b>Sample Part Number</b>	<b>ITS301</b>	<b>030</b>	<b>G</b>	<b>18</b>	<b>5E</b>	<b>1</b>	<b>F7</b>
<b>Basic Number</b>	<b>ITS301</b>						
<b>Connector Style<sup>1</sup></b>	<b>030</b> = Rear Panel Mount Square Flange Receptacle <b>01</b> = InLine Receptacle <b>070</b> = Rear Panel Mount Jam Nut Receptacle <b>06</b> = Straight Plug Connector						
<b>Insert-to-Shell Grounding</b>	<b>G</b> = Insert grounded to shell; available for receptacle only (for use with shielded cable) <b>Omit</b> = for none						
<b>Shell Size</b>	<b>18</b>						
<b>RJ45 Category</b>	<b>5E</b> = Cat 5E For Cat 6A applications consult factory						
<b>RJ45 Orientation</b>	<b>1, 2, 3</b> or <b>4</b>						
<b>Material/Finish</b>	<b>Omit</b> for Aluminum/Cadmium, Olive Drab (G3) <b>F6</b> = Aluminum/Black Polymer Electrocoat <b>F7</b> = Aluminum/Conductive Black Zinc Nickel <b>F11</b> = Aluminum/Electroless Nickel						

## RJ45 Orientation Options





Plug

Receptacle  
(In-Line Shown)


## NOTES

1. See Section A for panel cutout dimensions
2. Crimp removable size 22 contacts (M39029/58-360) supplied loose

## 06 - PLUG WITH ACCESSORY THREADS



## PLUG AND RECEPTACLE REAR TERMINATION VIEW






RJ45 CAT 5E ETHERNET

Series ITS (5015 type) Reverse-Bayonet




ITS301 Connector with Accessory Threads and Plug (Plug) or Jack (Receptacle) to Crimp Removable Contacts

**01 - INLINE RECEPTACLE WITH ACCESSORY THREADS**



**070 - REAR PANEL MOUNT JAM NUT RECEPTACLE WITH ACCESSORY THREADS**



**030 - REAR PANEL MOUNT SQUARE FLANGE RECEPTACLE WITH ACCESSORY THREADS**

