



USB 2.0 TYPE A

# Series ITS (5015 type) Reverse-Bayonet




ITS345 Connectors with USB Male (Plug) or Female (Receptacle) to Crimp Removable Contacts



How to Order							
<b>Sample Part Number</b>	<b>ITS345</b>	<b>06</b>	<b>16</b>	<b>2</b>	<b>A</b>	<b>H</b>	<b>F6</b>
<b>Basic Number</b>	<b>ITS345</b>						
<b>Connector Style<sup>1</sup></b>	<b>06</b> = Plug with Accessory Threads <b>01</b> = InLine Receptacle w/ Accessory Thd <b>070</b> = Rear Panel Mount Jam Nut Receptacle with Accessory Thread <b>030</b> = Rear Panel Mount Square Flange Receptacle with Accessory Threads						
<b>Shell Size</b>	<b>16</b>						
<b>USB Performance</b>	<b>2</b> = 2.0						
<b>USB Interface Type</b>	<b>A</b> = Type A						
<b>USB Orientation</b>	<b>H</b> = Horizontal <b>V</b> = Vertical						
<b>Material/Finish</b>	<b>Omit</b> for Al/Cadmium, Olive Drab (G3) <b>F6</b> = Al/Black Polymer Electrocoat <b>F7</b> = Al/Conductive Black Zinc Nickel <b>F11</b> = Al/Electroless Nickel						




### USB Orientation Options



### 06 - PLUG WITH ACCESSORY THREADS

#### Rear View

Horizontal USB Orientation  
Shown USB 2.0 Type A Male



#### NOTES

1. See Section A for panel cutout dimensions

E




USB 2.0 TYPE A

# Series ITS (5015 type) Reverse-Bayonet




ITS345 Connectors with USB Male (Plug) or Female (Receptacle) to Crimp Removable Contacts

## 01 - INLINE RECEPTACLE WITH ACCESSORY THREADS



## 070 - REAR PANEL MOUNT JAM NUT RECEPTACLE WITH ACCESSORY THREADS



## 030 - REAR PANEL MOUNT RECEPTACLE WITH ACCESSORY THREADS

