



**MIL-DTL-38999 Series III Type**

**600H005 Connector holding tool, plug and receptacle**



Dash Number, Torque and Dimensions						
Connector Shell Size	MIN/MAX IN-LB			A Dia Max	B Dia Max	C Dim Max
	Aluminum	Composite	Stainless Steel, High Vibration Applications			
09, A	30/40	20/25	91/101	.577 (14.7)	.438 (11.1)	1.031 (26.2)
11, B	30/40	20/30	115/125	.709 (18.0)	.566 (14.4)	1.031 (26.2)
13, C	35/45	25/35	115/125	.829 (21.1)	.678 (17.2)	1.031 (26.2)
15, D	35/45	25/35	139/149	.954 (24.2)	.803 (20.4)	1.031 (26.2)
17, E	35/45	30/40	139/149	1.107 (28.1)	.928 (23.6)	1.031 (26.2)
19, F	35/45	30/40	175/185	1.190 (30.2)	1.033 (26.2)	1.031 (26.2)
21, G	75/85	35/45	199/209	1.315 (33.4)	1.158 (29.4)	1.031 (26.2)
23, H	75/85	35/45	223/233	1.440 (36.6)	1.283 (32.6)	1.031 (26.2)
25, J	75/85	35/45	259/269	1.565 (39.8)	1.408 (35.8)	1.031 (26.2)

**NOTES**

1. Metric dimensions (mm) are indicated in parentheses.
2. Material: Case hardened carbon steel with electroless nickel finish.
3. Receptacle and plug holder drives: 1/4" - Shell sizes 09, 11 and 13; 3/8" - Shell sizes 15 and up.
4. Composite values apply when using Glenair 600-091 and 600-007 tools.