

HIGH TEMPERATURE ThermaRex HT Series 806 Accessories



Swing-Arm Saddle Clamp 870V001

THERMAREX™ HT



Self-locking, adjustable arms. 870V001 Swing-Arm saddle clamp fits Glenair Series 806 Mil-Aero connectors. Use with unshielded wire bundles. Adjustable arms pivot to 0°, 45° or 90° positions. Arms have self-locking threads to withstand high vibration. Full radius saddles have self-locking clinch nuts. Available in two clamp sizes: standard clamp fits most wire bundles, large clamp has increased clearance for oversize wire bundles. Coupling nut has anti-decoupling mechanism for audible detented coupling and prevents backoff under high vibration. Tested for 1000 hours at 300°C and in random vibration at 300°C.

MATERIAL/FINISH


Stainless Steel (Code Z1)

- Coupling nut, body, arms, saddles: SST
- Screws, washers, inserts: stainless steel/passivated
- Anti-decoupling springs: stainless steel
- Clinch Nuts: stainless steel, silver plated

How To Order

Sample Part Number	870V001	Z1	08	A
Series / Basic Part No.	870V001 Swing-Arm saddle clamp			
Material/Finish	Z1 = Stainless steel passivated			
Shell Sizes	08, 09, 10, 11, 12, 14, 16, 18, 20, 22, 24			
Clamp Size	A = Standard clamp B = Wide mouth			

Dimensions



Shell Size	A Thread ISO Metric	øC Max	D Max	E Max	F Max	G Max	H Max	J Ref.
08	M10 x 1.0-6H	.812 (20.62)	1.55 (39.37)	1.45 (36.83)	.77 (19.56)	.98 (24.89)	.87 (22.10)	.393 (9.98)
09	M12 x 1.0-6H	.812 (20.62)	1.55 (39.37)	1.45 (36.83)	.77 (19.56)	.98 (24.89)	.87 (22.10)	.393 (9.98)
10	M14 x 1.0-6H	.938 (23.83)	1.61 (40.89)	1.56 (39.62)	.87 (22.10)	1.05 (26.67)	.96 (24.38)	.455 (11.56)
11	M15 x 1.0-6H	.938 (23.83)	1.61 (40.89)	1.56 (39.62)	.87 (22.10)	1.05 (26.67)	.96 (24.38)	.455 (11.56)
12	M17 x 1.0-6H	1.125 (28.58)	1.66 (42.16)	1.71 (43.43)	.97 (24.64)	1.22 (30.99)	1.03 (26.16)	.598 (15.19)
14	M19 x 1.0-6H	1.250 (31.75)	1.67 (42.42)	1.79 (45.47)	1.02 (25.91)	1.32 (33.53)	1.10 (27.94)	.710 (18.03)
16	M22 x 1.0-6H	1.250 (31.75)	1.67 (42.42)	1.79 (45.47)	1.02 (25.91)	1.32 (33.53)	1.10 (27.94)	.710 (18.03)
18	M25 x 1.0-6H	1.375 (34.92)	1.77 (44.96)	1.88 (47.75)	1.08 (27.43)	1.38 (35.05)	1.16 (29.46)	.839 (21.31)
20	M28 x 1.0-6H	1.500 (38.10)	1.77 (44.96)	1.96 (49.78)	1.13 (28.70)	1.49 (37.85)	1.22 (30.99)	.934 (23.72)
22	M31 x 1.0-6H	1.625 (41.28)	1.92 (48.77)	2.13 (54.10)	1.24 (31.50)	1.61 (40.89)	1.29 (32.77)	1.068 (27.13)
24	M34 x 1.0-6H	1.750 (44.45)	1.95 (49.53)	2.20 (55.88)	1.30 (33.02)	1.68 (42.67)	1.36 (34.54)	1.197 (30.40)

Swing-Arm Saddle Clamp 870V001

THERMAREX™ HT

