



# Space-Grade, High-Speed Circular, Blind-Mate Connectors



**Application:** Glenair Series 253 blind-mate connectors are designed to meet applicable environmental, electrical and mechanical performance characteristics of D38999 Series III. The technology is well suited for use in commercial rack-and-panel instrumentation applications, as well as a blind-mate solution for satellite deployment, scientific research and development payloads, interstage, UAV, and munitions release and more.

- **Blind-mate, fixed and float-mount interconnects for non-ITAR commercial as well as military/defense applications**
- **Adjustable separation force (AKA assisted-release, zero extraction force) solutions**
- **Misalignment accommodation and special auxiliary sealing for trouble-free blind mating in environmental applications**
- **Available in most symmetrical MIL-STD-1560 insert arrangements with contacts sizes from #23 to #8**
- **Selected materials offer low outgassing properties and high resistance to both corrosion and stress corrosion cracking**
- **NASA outgassing bake-out process available**
- **Designed to withstand the rigors of launch and flight—including shock, vibration, thermal vacuum, acceleration, and temperature extremes**
- **Standard accessory threads and teeth per MIL-DTL-38999 accommodate a wide range of backshell accessories**
- **Crimp-removable contacts standard. Consult factory for PC tails, dual-flange standoffs, custom blind-mate configurations, and hermetically sealed options**

Current Rating	
Size Contact	Amps
23	5
22D	5
20	7.5
16	13
12	23

Unmated Test Voltages, AC RMS, 60 Hz				
Altitude (Feet)	Service Rating M	Service Rating N	Service Rating I	Service Rating II
Sea Level	1300	1000	1800	2300
50,000	550	400	600	800
70,000	350	260	400	500
100,000	200	260	200	200