

"ZERO-CROSSTALK" M83513 Micro-D VersaLink™ Connectors



GVLM-BR Right-Angle PCB Connectors

MATERIALS AND FINISHES



- Connector shell: aluminum alloy 6061
- Insulator (v): rigid dielectric
- Insulator (m): liquid crystal polymer (LCP) or polyphenylene sulfide (PPS)
- Flange seal: fluorosilicone rubber, blue
- Pin contact:
copper alloy, gold over nickel plating
- Socket contact: copper alloy, gold over nickel plating
- Ground spring: stainless steel, gold plating
- Hardware: 300 series stainless steel, passivated
- Encapsulant: epoxy resin Hysol EE4215

PERFORMANCE SPECIFICATIONS

- Current rating: 3 amp (Micro-D contacts)
- DWV: 600 VAC sea level
- Insulation resistance:
5000 megohms minimum
- Operating temperature: -55° C to +150° C
- Mating force (contact m):
(10 ounces) x (# of contacts)
- Mating force (contact v):
(5 ounces) x (# of contacts)
- Electrical performance IAW Glenair specification GT-19-230
- Interface dimensions IAW MIL-DTL-83513
- Reference application notes AN0005 for optimal performance


NOTES

- Refer to GHS4-M-1000 for insert arrangement details on page 94.
- Refer to GVLM-1001 for GVLM-BR PCB footprints on page 123.
- Recommended mating dimensions must be maintained when no hardware is used, see page 95.
- Plug connector uses pin Micro-D contacts and socket VersaLink contacts. Receptacle uses socket Micro-D contacts and pin VersaLink contacts.
- Hardware always required to ensure connector pair is fully mated when installed.
- PC tails are solder-dipped in 60/40 tin-lead solder.
- Refer to 500-154 for protective cover on page 164.



PART NUMBER DEVELOPMENT									
Sample Part Number	GVLM	2	L-	2-9	P	BR	P	T	-.110
Series	GVLM = VersaLink Micro-D								
Shell Finish	2 = Nickel 5 = Gold								
Insulator Material	L = LCP or PPS								
Contact Layout (V-M) ¹	1-0, 1-9, 2-0, 2-9, 2-15, 2-21, 3-9, 4-0, 4-15, 4-31, 8-9, 10-0								
Connector Type ⁴	P = Plug S = Receptacle								
Connector Style	BR = Board Right Angle								
Hardware ^{3,5} (see mounting hardware table)	P = Jackpost L = Hex head jackscrew (non-removable)								
	Panel Mount Jackposts:								
	R1 = .032 panel R2 = .047 panel								
	R3 = .062 panel R4 = .093 panel								
	R5 = .125 panel R6 = .080 panel								
Threaded Insert Option	T = Threaded insert in board-mount hole (required for L hardware) Omit for thru-hole								
PC Tail Length ⁶	.080, .110, .140 (Length in Inches +.020/-.000)								

HARDWARE



INSERT ARRANGEMENTS

Insert Arrangements	No. of Contacts	
	VersaLink (V)	TwistPin (M)
1-0	1	0
2-0	2	0
1-9	1	9
2-9	2	9
4-0	4	0
2-15	2	15
2-21	2	21
3-9	3	9
4-15	4	15
4-31	4	31
8-9	8	9
10-0	10	0


"ZERO-CROSSTALK" M83513 Micro-D VersaLink™ Connectors




GVLM-BR Right-Angle PCB Connectors

MICRO-D VERSALINK CONNECTORS

GVLM PCB RIGHT ANGLE PLUG CONNECTOR



GVLM PCB RIGHT ANGLE RECEPTACLE CONNECTOR



PLUG DIMENSIONS

LAYOUT	A MAX	B	C MAX	G
1-0P	0.785 (19.94)	0.565 (14.35)	0.333 (8.46)	0.350 (8.89)
2-0P	0.935 (23.75)	0.715 (18.16)	0.483 (12.27)	0.500 (12.70)
1-9P	1.085 (27.56)	0.865 (21.97)	0.633 (16.08)	0.650 (16.51)
2-9P	1.185 (30.10)	0.965 (24.51)	0.733 (18.62)	0.750 (19.05)
4-0P	1.185 (30.10)	0.965 (24.51)	0.733 (18.62)	0.750 (19.05)
2-15P	1.335 (33.91)	1.115 (28.32)	0.833 (21.16)	0.900 (22.86)
2-21P	1.485 (37.72)	1.265 (32.13)	1.033 (26.24)	1.050 (26.67)
3-9P	1.485 (37.72)	1.265 (32.13)	1.033 (26.24)	1.050 (26.67)
4-15P	1.835 (46.61)	1.615 (41.02)	1.384 (35.15)	1.400 (35.56)
4-31P	2.235 (56.77)	2.015 (51.18)	1.784 (45.31)	1.800 (45.72)
8-9P	2.235 (56.77)	2.015 (51.18)	1.784 (45.31)	1.800 (45.72)
10-0P	2.235 (56.77)	2.015 (51.18)	1.784 (45.31)	1.800 (45.72)

RECEPTACLE DIMENSIONS

LAYOUT	A MAX	B	C MAX	G
1-0S	0.785 (19.94)	0.565 (14.35)	0.400 (10.16)	0.350 (8.89)
2-0S	0.935 (23.75)	0.715 (18.16)	0.551 (14.00)	0.500 (12.70)
1-9S	1.085 (27.56)	0.865 (21.97)	0.701 (17.81)	0.650 (16.51)
2-9S	1.185 (30.10)	0.965 (24.51)	0.801 (20.35)	0.750 (19.05)
4-0S	1.185 (30.10)	0.965 (24.51)	0.801 (20.35)	0.750 (19.05)
2-15S	1.335 (33.91)	1.115 (28.32)	0.951 (24.16)	0.900 (22.86)
2-21S	1.485 (37.72)	1.265 (32.13)	1.101 (27.97)	1.050 (26.67)
3-9S	1.485 (37.72)	1.265 (32.13)	1.101 (27.97)	1.050 (26.67)
4-15S	1.835 (46.61)	1.615 (41.02)	1.450 (36.83)	1.400 (35.56)
4-31S	2.235 (56.77)	2.015 (51.18)	1.850 (46.99)	1.800 (45.72)
8-9S	2.235 (56.77)	2.015 (51.18)	1.850 (46.99)	1.800 (45.72)
10-0S	2.235 (56.77)	2.015 (51.18)	1.850 (46.99)	1.800 (45.72)