

## Ultra high-temperature stainless steel flexible metal-core EMI/RFI conduit 750-190


THERMAREX™ UHT



How To Order			
Sample Part Number	750-190	-047	C
Series / Basic Part No.	750-190 Ultra High-temperature ThermaRex Flexible Metal-Core Conduit		
Dash No.	See Table I		
Core Option	C = Stainless steel		

Std. Conduit Tolerances	
Length (Inches)	Tolerance (Inches)
Up To 18	± .50
19 - 36	± 1.0
37 - 72	± 1.5
73 - 144	± 2.0
145 - 300	± 3.0
301 - 600	± 4.0
601 - 1200	± 5.0
1201 - Up	± 6.0

Table I: Dash No. / Dimensions			
Dash No.	A I.D.	B O.D.	
	Min	Min	Max
06	.175 (4.45)	.260 (6.60)	.270 (6.86)
08	.245 (6.22)	.354 (9.00)	.374 (9.50)
09	.294 (7.47)	.390 (9.91)	.398 (10.1)
10	.308 (7.82)	.408 (10.4)	.425 (10.8)
12	.370 (9.40)	.478 (12.1)	.498 (12.6)
16	.495 (12.6)	.627 (15.9)	.647 (16.4)
20	.620 (15.7)	.750 (19.1)	.770 (19.6)
24	.745 (18.9)	.870 (22.1)	.890 (22.6)
32	.995 (25.3)	1.182 (30.0)	1.202 (30.5)
40	1.245 (31.6)	1.444 (36.7)	1.464 (37.2)
48	1.495 (38.0)	1.694 (43.0)	1.714 (43.5)
56	1.760 (44.7)	1.970 (50.0)	1.985 (50.4)
64	1.995 (50.7)	2.204 (56.0)	2.224 (56.5)
80	2.495 (63.4)	2.704 (68.7)	2.724 (69.2)
96	2.995 (76.1)	3.194 (81.1)	3.214 (81.6)



### PACKAGING

Long-length orders of 750-190 conduit are subject to carrier weight and box size restrictions. For example, UPS air shipments are currently limited to 50 lbs. per box.

Unless otherwise specified, Glenair standard practice is to ship optimal lengths of product based on weight, size, and individual carrier specifications. Consult factory for additional information or to specify packaging requirements.