



**600G005**  
**MIL-DTL-28840 and MIL-PRF-28876**  
**Plug and Receptacle Holder**



| Shell Size | Max. Recommended Torque (Inch Pounds) | A Dia. Max.  | B Dia. Max.  | C Dim. Max. |
|------------|---------------------------------------|--------------|--------------|-------------|
| 11         | 80                                    | .697 (17.7)  | .502 (12.8)  | .945 (24.0) |
| 13         | 110                                   | .822 (20.8)  | .626 (15.9)  | .945 (24.0) |
| 15         | 120                                   | .995 (25.3)  | .798 (20.3)  | .945 (24.0) |
| 17         | 120                                   | 1.058 (26.9) | .868 (22.0)  | .945 (24.0) |
| 19         | 120                                   | 1.245 (31.6) | 1.035 (26.3) | .945 (24.0) |
| 23         | 140                                   | 1.433 (36.4) | 1.220 (31.0) | .945 (24.0) |
| 25         | 140                                   | 1.558 (39.6) | 1.381 (35.1) | .945 (24.0) |
| 29         | 150                                   | 1.745 (44.3) | 1.547 (39.3) | .945 (24.0) |
| 33         | 150                                   | 1.933 (49.1) | 1.739 (44.2) | .945 (24.0) |

**APPLICATION NOTES**

1. Metric dimensions (mm) are indicated in parentheses.
2. Material: Case hardened carbon steel with electroless nickel finish.
3. Receptacle and plug holder drives: 1/4" - Shell sizes 08, 10, 12; 3/8" - Shell sizes 14 and up.
4. For MIL-Spec and Commercial Equivalent Backshells/Accessories for use with MIL-PRF-28876 Connectors, see MIL-STD-2042/5 for Torque Values.
5. If using Thread Locker to secure the Backshell/Accessory threads to the Connector, Torque Values less than those shown in the table may be considered, and shall be highly evaluated before using in the intended application.